

PI-640<規格表>

赤枠内の表記を修正

型式		曲げ半径 選択	リンク数	H (取付高さ)	H <sub>1</sub>	HF (必要空間高さ)	K (円弧+余裕値)	P	B	ℓ
Type	No.									
SE045F SZ045F	16	018	1~27	50	37.5	60	95	13	12.5	22.3
		028	1~29	70	57.5	80	120			
		038	1~31	90	77.5	100	145			
SE08F SZ08F	16	028	1~37	76	56.7	91	130	20	19.3	28
	20	038	1~38	96	76.7	111	160			
	30									
	40									
50	048	1~40	116	96.7	131	190				
SE14F SZ14F	1	028	1~30	82	57	92	150	30.5	25	38
	2	038	1~30	102	77	112	185			
	3	048	1~30	122	97	132	215			
	4	075	1~30	177	152	187	300			
		100	1~33	227	202	237	375			
SE16F SZ16F	2	060	1~30	159	120	174	270	30.5	39	38
	3	075	1~30	189	150	204	305			
		100	1~33	239	200	254	395			
	4	055	1~28	145	110	185	276			

<訂正用>

P	B	ℓ
13	12.5	22.3
20	19.3	28
30.5	25	38
30.5	39	38