

P.698 <規格表>

赤枠内の表記を訂正

型式		H										ミスミ適用ボールねじ																	
Type	No.	選択										A	B	P.C.D.	K	M1×ℓ	D	ℓ1	F	L	ℓ2	ℓ3	M2×ℓ	BSX (C3)	BSS (C5) BSSE (C7)	BS □□□ (C10)			
	801X	10	20									30	H+8	19	30			12.4	24	8	16	3	10	M3×5	0801	—	—		
	802S	18	20	23	25							40	H+13	27	45	M3×5	20.4	30	14	28	8			M3×5	0802	0802	—		
	802C	17	20	23	25								H+10	24	30	M4×7	16.4		12					M4×8	—	—	0802		
	802R	17	20	23	25	28	30						H+12	24	30	M4×7	20.4	34	17		24	6	12	M4×8	—	—	0802		
	804R	17	20	23	25	28	30					43	H+12	24	30	M3×5	20.4	34			24	6	12	M4×8	—	—	0804		
	1002R	17	20	23	25	28	30					50	H+13.5	33	30	M3×5								M4×8	—	—	1002		
	1002X	17	20	23	25	28	30						H+13.5	33	30	M3×5	23.4	42			16			M4×8	—	—	1002		
	1002S	17	20	23	25	28	30	35	40			43	H+15.5	31	45	M3×5		34				26	7	M4×8	—	—	1002		
	1004S	20	23	25	28	30	35	40				52	H+14	36	45	M4×7	26.4	42	22	32	10	16		M5×10	—	—	1004		
	1004C	17	20	23	25	28	30	35	40			50	H+13	31	30	M4×7	22.4	40	18			24	6	M5×10	—	—	1004		
	1004R	17	20	23	25	28	30	35	40				H+14		30	M4×7	26.4		22		27	6	15	M5×10	—	—	1004		
	1010R	17	20	23	25	28	30	35	40			52	H+15	36	30	M4×7	28.4	42		23		34	7	20	M5×10	—	—	1010	
	1010S	17	20	23	25	28	30	35	40				H+15		30	M4×7	28.4				23		34	7	20	M5×10	—	—	1010
	1202S	20	23	25	28	30	35	40				50	H+17	33	45	M5×7	25.4	40	15	28	8	14		M5×10	1202	1202	—		
	1204S	20	23	25	28	30	35	40				52	H+20.5	41	45	M5×7	30.4		20		34	7	20	M5×10	—	—	1204		
	1204C	20	23	25	28	30	35	40					H+14	33	30	M4×7	24.4	42			27	6	15	M5×10	—	—	1204		
	1204R	20	23	25	28	30	35	40					H+15	40	30	M4×7					29	7		M5×10	—	—	1204		
	1205S	20	23	25	28	30	35	40					H+15	40	30	M4×7					29	7		M5×10	—	—	1204		
	1210S	20	23	25	28	30	35	40				60	H+16	41	45	M5×7	30.4	50	24		36	8		M6×12	—	—	1210		
	1405R	20	23	25	28	30	35	40					H+16	40	30	M4×7					40	10		M6×12	—	—	1405		
	1505C	20	23	25	28	30	35	40	45				H+16	42	45	M5×7	31.4				34	7	20	M6×12	—	—	1505		
	1505R	20	23	25	28	30	35	40	45				H+16	42	45	M4×7					34	7		M6×12	—	—	1505		
	1505S	20	23	25	28	30	35	40	45				H+17	45	45	M4×7	34.4		28		36	8		M6×12	1505	1505	—		
	1510S	20	23	25	28	30	35	40	45				H+17	40	30	M5×7					42	11		M6×12	—	—	1510		
	1510C	20	23	25	28	30	35	40	45			62	H+17	42	45	M5×7	31.4	52		24	38		7	24	M6×12	—	—	1510	
	1510R	20	23	25	28	30	35	40	45				H+17	45	45	M5×7	34.4		28		44			30	M6×12	—	—	1510	
	1520S	23	25	28	30	35	40	45					H+19	49	30	M6×10					50			34	M6×12	—	—	1520	
	2005C	25	28	30	35	40	45					72	H+19	49	45	M6×10	36.4	60	26	40		40	20	M8×16	—	—	2005		
	2010C	25	28	30	35	40	45					76	H+20	53	45	M6×10		64			34	40	20	M8×16	—	—	2010		
	2005S	25	28	30	35	40	45						H+20	53	45	M4×7	40.4		56		32	40	20	M8×16	—	—	2005		
	2005R	25	28	30	35	40	45						H+19.5	50	45	M5×7					70	15	40	M8×16	—	—	2005		
	2020R	25	28	30	35	40	45					68	H+19.5	50	45	M6×10	42.4	64		32	40	40		M10×20	—	—	2020		
	2505C	28	30	35	40	45	55						H+24	53	45	M6×10	43.4	62	38	60		35	40	M10×20	—	—	2505		
	2505R	28	30	35	40	45	55					76	H+21	55	45	M5×7	46.4		70	40	90		20	M8×16	—	—	2505		
	2010S	28	30	35	40	45	55						H+23	59	45	M6×10	47.4		64	32	40	40		M10×20	2010/2020	—	—		
	2525R	28	30	35	40	45	55					82	H+23	60	45	M6×10	47.4		64	32	40	40		M8×16	—	—	2525		
	2505S	30	35	40	45	55						76	H+28.5	60	45	M6×10	47.4		64	32	40	40		M8×16	—	—	2505		
	2010R	35	40	45	55							84	H+26	67	45	M8×12	52.4		72	46	60	40		M10×20	—	—	2010		
	2510S	35	40	45	55							94	H+26	68	45	M8×12	52.4		80	44	55	35		M10×20	—	—	2510/2520		
	2510R	35	40	45	55							100	H+30	78	45	M6×10	60.4	86	54	60		40		M8×16	—	—	2510		
	2806R	35	40	45	55							87	H+26	65	45	M6×10	50.4	75	42	60		40		M8×16	—	—	2806		
	3232R	35	40	45	55							106	H+30	74	45	M8×12	58.4	86	50	75		55		M10×20	—	—	3232		
	3210R	40	45	55								116	H+33	85	45	M8×12	67.4	96	58	80		60		M10×20	—	—	3210		

●No.802Rは、2つ穴になります。 ●No.□□□□CはC10転造ボールねじコンパクトタイプ用になります。

<訂正用>

