

シャフト 両端おねじパイプタイプ C寸法表記を一部修正

Catalog No.		指定1mm単位			P・Q 選択	d	(Y) Max.	R	C	
Type	Dg6	L	F・T	B・S						
SPJM RSPJM (D \leq 30、L \leq 500) PSPJM	6	-0.004 -0.012	25~596	$2 \leq F \leq P \times 5$ $2 \leq T \leq Q \times 5$	$B \leq F - 2$ (P \leq 6のとき)	6	2	600	0.3 以下	0.5 以下
	8	-0.005	25~796		$B \leq F - 3$ (P=8・10のとき)	8	3	800		
	10	-0.014	25~796		$B \leq F - 5$ (P \geq 12のとき)	8 10	4	800		
	12	-0.006 -0.017	25~996		$B = 0$ (ねじなしのとき)	10 12	6	1000		
	13		25~996		$S \leq T - 2$ (Q \leq 6のとき)	12	7	1000		
	16	-0.007 -0.020	25~1196		$S \leq T - 3$ (Q=8・10のとき)	16	10	1200		
	20		25~1196		$S \leq T - 5$ (Q \geq 12のとき)	20	14	1200		
	25		25~1196		$S = 0$ (ねじなしのとき)	24	16	1200		
	30		25~1496			24 30	17	1500		
	35	-0.009	25~1496			30	19	1500	0.5 以下	1.0 以下
40	-0.025	25~1496		30	20	1500				

<訂正用>

0.5
以下