

ノーマルタイプ 赤枠内の数値を修正

## ■ ノーマル

D	¥単価 1~4コ 丸形状							¥単価1~4コ ダイヤ形状						
	①SKS3焼 KFA	②SKS3硬質 GKFA	③SKS3 BKFA	④SUS304 SKFA	⑤SUS304硬質 HKFA	⑥SUS440C CKFA	⑦SCM415 TKFA	①SKS3焼 KFD	②SKS3硬質 GKFD	③SKS3 BKFD	④SUS304 SKFD	⑤SUS304硬質 HKFD	⑥SUS440C CKFD	⑦SCM415 TKFD
1	2,260	3,050	2,040	3,210	3,860	3,570	—	1,200	1,620	1,120	1,650	2,640	1,870	—
2	860	1,160	780	1,240	1,490	1,400	—	1,120	1,510	1,010	1,600	1,920	1,810	—
3	920	1,240	830	1,320	1,600	1,480	1,060	1,220	1,640	1,100	1,700	2,040	1,920	1,410
4	1,010	1,360	910	1,440	1,730	1,620	1,170	1,330	1,790	1,200	1,860	2,230	2,090	1,530
5	1,100	1,480	990	1,560	1,870	1,760	1,270	1,420	1,910	1,280	2,020	2,430	2,280	1,640
6	1,150	1,550	1,040	1,640	1,980	1,840	1,330	1,500	2,020	1,350	2,150	2,570	2,400	1,730
8	1,220	1,640	1,100	1,730	2,070	1,920	1,410	1,590	2,140	1,440	2,240	2,690	2,510	1,830
10	1,260	1,700	1,140	1,810	2,180	2,030	1,450	1,640	2,210	1,480	2,370	2,840	2,610	1,890
12	1,330	1,790	1,200	1,890	2,270	2,030	1,530	1,740	2,340	1,570	2,470	2,960	2,650	2,010
13	1,390	1,870	1,260	1,980	2,380	2,200	1,600	1,790	2,410	1,620	2,570	3,090	2,660	2,060
16	1,840	2,480	1,660	2,640	3,170	2,950	2,120	2,400	3,240	2,160	3,430	4,110	3,850	2,760
20	2,340	3,150	2,110	3,340	4,010	3,730	2,700	3,030	4,090	2,730	4,360	5,230	4,850	3,490

&lt;訂正用&gt;

¥単価1~4コ ダイヤ形状		
③SKS3 BKFD	④SUS304 SKFD	⑤SUS304硬質 HKFD
1,120	1,650	2,640
1,010	1,600	1,920
1,100	1,700	2,040
1,200	1,860	2,230
1,280	2,020	2,430
1,350	2,150	2,570
1,440	2,240	2,690
1,480	2,370	2,840
1,570	2,470	2,960
1,620	2,570	3,090
2,160	3,430	4,110
2,730	4,360	5,230