

P.1934 (規格表)

SQNS4のA寸28～36にT寸2.0追加

型式		A	P 選択	B	T		SQN ¥単価				SQNS ¥単価			
Type	M				SQN	SQNS	1~49□	50~99	100~499	500~	1~4□	5~19	20~49	50~
SQN SQNS	2	15	8	4.0	1.6	1.5	195	150	125	99	400	380	360	340
		25	18											
	3	15	6 6.5 7	5.4	2.3	2.0	135	90	75	59	330	310	300	280
		20	8 9 10 12											
		25	14 16 18 19 20											
		32	22 24 24.5											
	4	28	*16 (16.5) (18)	6.8	3.2	2.0	150	105	88	69	500	480	450	430
		32	*20 (22) (23)											
		36	*25 (25.4)											
		52	(33) (40) (42)											
	5	40	25 28	7.8	3.2	—	180	135	113	89	—	—	—	—
		42	30 30.2											
		52	32 40 42											
		72	50 54 60											

④SQNS M4は、
()寸法は
選択不可

*印はSQNS規格追加

<訂正用>

