

## P2202 (規格表)

赤枠内 数値を変更

Catalog No.		d	H	W	許容荷重 N	質量 (g)	適用キャスト	¥単価
Type	D							1~9コ
RMNA (ゴム)	75	10	36	32	800	200	CMGJ CMGK CMGS (P.2201)	400
	100	12	42		1200	410		450
	130	20	52	38	1800	750		720
	150		55	42	2000	1000		820
RNTB (ウレタン)	75	10	35	32	1200	290		1,300
	100	12	42		1700	590		1,380
	130	20	52	38	2600	960		2,200
	150		55	42	3000	1280		2,540
RVA (モノマーキャストینگナイロン)	75*	10	35.6	32	3600	200		1,540
	100	12	41	34	5200	480		2,160
	130	20	52	42	8400	790		4,150
	150		55	44	10000	1060		4,560

&lt;訂正用&gt;

3600
5200
8400
10000