

## P.1003 &lt;規格表&gt;

赤枠内区切り位置を修正

Catalog No.		最大長 (Lmax)	最小長 (Lmin)	ストローク	ガス反力 (20℃)		A	B	C	G	H	適合取付 ブラケット	重量 (g)	¥単価
Type	No.				最大長-10mm時 (kgf)	最大長-( )mm時 (kgf)								1~4本
	15050A	246	196	50	5	7 (40)	15	7			164		125	1,790
	15050B				10	13 (40)								
	15080A	330	250	80	5	7 (70)								
	15080B				10	13 (70)								
	15090A	360	270	90	5	7 (80)								
	15090B				10	13 (80)								
	15100A	386	286	100	5	7 (90)								
	15100B				10	13 (90)								
	18100A	386	286	100	20	26 (90)	18	8			253	210	2,030	
	18100B				30	39 (90)								
	18150A	526	376	150	20	27 (140)								
	18150B				30	40 (140)								
	22050A	246	196	50	20	27 (40)				163		215	2,030	
	22050B				30	41 (40)								
	22050C				40	54 (40)								
	22080A	330	250	80	20	28 (70)				217		270	1,920	
	22080B				30	42 (70)								
	22080C				40	55 (70)								