

P.1517<規格表>

赤枠内の色変更 (数値に変更はありません)

■P□Mタイプ (両サイドベアリングタイプ)

Catalog No.			軸径 d	P.D.	O.D.	F	E	A	W	Dh	ベアリング寸法			¥単価 1~4コ	
Type	歯数	対応ベルト									No.	D	B		
BPTFW	25	P5M100	6	39.79	38.65	45	33.5	11.6	16	13	696ZZ×2	15	5	5,890	
		P5M150						16.6	21					6,050	
	25	P5M100	8	39.79	38.65	45	33.5	11.6	16	16.5	698ZZ×2	19	6	6,050	
		P5M150						16.6	21					6,210	
	28	P5M100	10	44.56	43.42	52	37.5	11.6	16	19.5	6900ZZ×2	22	6	7,000	
		P5M150						16.6	21					7,160	
		30	P5M150	12	47.75	46.60	55	42.5	16.6	21	24	6001ZZ×2	28	8	6,880
		36	P5M150	15	57.30	56.15	64	50	16.6	21	28	6002ZZ×2	32	9	7,870
		26	P8M150	12	66.21	64.84	73	56	16.8	22	24	6001ZZ×2	28	8	9,370
			P8M250						27.8	33					10,370
		30	P8M150	15	76.39	75.02	82	67	16.8	22	28	6002ZZ×2	32	9	10,070
			P8M250						27.8	33					11,340
	30	P8M250	20	76.39	75.02	82	67	27.8	33	36	6004ZZ×2	42	12	11,700	