

規格表内、G寸法条件を一部追加（赤枠参照）

■穴加工付タイプ

Catalog No.		W						L	H	P	G		ボルト穴呼び径指定						
Type	T	選択						指定1mm単位	(穴数)	指定1mm単位	固定	指定 指定1mm単位	Z		ZN				
NLBB NLBBF	3	10	15	20	25						W/2	7~20 d ₁ /2+1 ≤ G ≤ W/2 (NLBBFのみ適用)	—		4				
	5		15	20	25	30	35						—		4 5 6				
	8			20	25	30	35	40						3	4	5	4	5	6
	10			20	25	30	35	40						4	5	6	5 6		
	15				25	30	35	40						4	5	6	8	—	
	20					30	35	40						4	5	6	8	—	

① $\{L - P(H - 1)\} / 2 \geq d_1 / 2 + 2$