

# 油圧・水圧用継手

—ストレートタイプ—

CADデータフォルダ名: 52\_Pipes\_Fitting\_Valves

**PT・PT両オネジ**  
—ストレート—

Type: YCPT, YCPTS  
M材質: S35C, SUS304  
S表面処理: 三価クロメート

型式 Type	No.	T1 R(PT)	T2 R(PT)	L	l1	l2	B	¥基準単価	
								YCPT	YCPTS
11	1/8	1/8	26	10	10	12	200	650	
12	1/8	1/4	31	10	13	17	260	660	
13	1/8	3/8	33	10	15	21	270	—	
22	1/4	1/4	34	13	13	17	280	680	
23	1/4	3/8	36	13	15	21	280	690	
33	3/8	3/8	37	15	15	21	290	720	
34	3/8	1/2	40(46)	14(16)	17(19)	26(22)	450	1,300	
44	1/2	1/2	43	17	17	26(22)	460	1,250	
46	1/2	3/4	46(48)	17(18)	19	32(27)	650	1,430	
66	3/4	3/4	48	19	19	32(27)	680	1,530	

**PT・PF両オネジ**  
—ストレート・オス—

Type: YCPFP, YCPFSP  
M材質: S35C, SUS304  
S表面処理: 三価クロメート

型式 Type	No.	T R(PT)	F G(PF)	L	l1	l2	B	¥基準単価	
								YCPFP	YCPFSP
11F	1/8	1/8	31	10	13	14	200	650	
12F	1/8	1/4	34	10	16	19	240	660	
13F	1/8	3/8	37	10	17.5	22	280	—	
21F	1/4	1/8	34	13	13	14	310	680	
22F	1/4	1/4	37	13	16	19	320	700	
23F	1/4	3/8	38.5	13	17.5	22	330	720	
31F	3/8	1/8	37	15	13	19	340	—	
32F	3/8	1/4	38.5	15	16	19	350	740	
33F	3/8	3/8	40.5	15	17.5	22	360	760	
34F	3/8	1/2	45	15	20	27	410	1,130	
44F	1/2	1/2	48	18	20	27	470	1,180	
46F	1/2	3/4	52	18	22	32	780	2,040	
64F	3/4	1/2	50	20	20	27	780	2,040	
66F	3/4	3/4	54	20	22	36	800	2,080	

**PTオネジ・PFメネジ**  
—ストレート・メス—

Type: YCPFGP  
M材質: S35C  
S表面処理: 三価クロメート

型式 Type	No.	T R(PT)	F G(PF)	L	l1	l2	B	¥基準単価	
								YCPFGP	—
22F	1/4	1/4	38	13	8	19	520	—	
33F	3/8	3/8	42	15	8	22	610	—	
44F	1/2	1/2	50	18	10	27	830	—	

**PTメネジ・PFオネジ**  
—ストレート・オス—

Type: YCPFFP, YCPFFSP  
M材質: S35C, SUS304  
S表面処理: 三価クロメート

型式 Type	No.	T Rc(PT)	F G(PF)	L	l1	B	¥基準単価	
							YCPFFP	YCPFFSP
22F	1/4	1/4	33	16	19	380	830	
33F	3/8	3/8	37	18	22	490	970	
44F	1/2	1/2	42	20	27	560	1,350	

仕様 使用流体 油・水  
最高使用圧力 20.6MPa(210kg/cm<sup>2</sup>以下)

**PT・PF両オネジ**  
—ストレート・メス—

Type: YCPF, YCPFS  
M材質: S35C, SUS304  
S表面処理: 三価クロメート

型式 Type	No.	T R(PT)	F G(PF)	L	l1	l2	B	¥基準単価	
								YCPF	YCPFS
11F	1/8	1/8	27	10	11	14	200	650	
12F	1/8	1/4	32	10	13	19	240	660	
13F	1/8	3/8	34	10	15	22	280	—	
21F	1/4	1/8	32	13	11	14	310	680	
22F	1/4	1/4	34	13	13	19	320	700	
23F	1/4	3/8	36	13	15	22	330	720	
31F	3/8	1/8	34	15	11	19	340	—	
32F	3/8	1/4	36	15	13	19	350	740	
33F	3/8	3/8	38	15	15	22	360	760	
34F	3/8	1/2	42	15	17	27	410	1,130	
44F	1/2	1/2	47	18	18	27	470	1,180	
46F	1/2	3/4	50	18	20	32	780	2,040	
64F	3/4	1/2	47	20	17	27	780	2,040	
66F	3/4	3/4	53	20	20	36	800	2,080	

**PTオネジ・PFメネジ**  
—ストレート・オス—

Type: YCPFG, YCPFGS  
M材質: S35C, SUS304  
S表面処理: 三価クロメート

型式 Type	No.	T R(PT)	F G(PF)	L	l1	l2	B	¥基準単価	
								YCPFG	YCPFGS
11F	1/8	1/8	31	10	6	14	280	1,400	
12F	1/8	1/4	34	10	8	19	420	—	
21F	1/4	1/8	34	13	6	14	440	—	
22F	1/4	1/4	36	13	8	19	460	1,080	
23F	1/4	3/8	39	13	8	22	480	—	
32F	3/8	1/4	39	15	8	19	520	—	
33F	3/8	3/8	42	15	8	22	540	1,200	

**PTメネジ・PFオネジ**  
—ストレート・メス—

Type: YCPFF, YCPFFS  
M材質: S35C, SUS304  
S表面処理: 三価クロメート

型式 Type	No.	T Rc(PT)	F G(PF)	L	l1	B	¥基準単価	
							YCPFF	YCPFFS
22F	1/4	1/4	30	13	19	380	830	
33F	3/8	3/8	34	15	22	490	970	
44F	1/2	1/2	40	18	27	560	1,350	

**PT・PF両オネジ**  
—ロングストレート・メス—

Type: YCLPF  
M材質: S35C  
S表面処理: 三価クロメート

型式 Type	No.	T R(PT)	F G(PF)	L	l1	B	¥基準単価	
							YCLPF	—
22F	1/4	1/4	75	13	19	1,040	—	
33F	3/8	3/8	78	15	22	1,250	—	
44F	1/2	1/2	93	18	27	1,380	—	

Order 注文例 YCPT11 Price 価格 数量スライド価格 (※1円未満切り捨て) P89  
数量 1~9 10~19 20~29  
値引率 基準単価 5% 10%

Delivery 出荷日 在庫品 翌日出荷 翌日 P89  
ご希望によりJIS5000迄、当日出荷受付け致します。

# 油圧・水圧用継手

—ストレートタイプ・45°エルボタイプ・エルボタイプ—

CADデータフォルダ名: 52\_Pipes\_Fitting\_Valves

**PT・PF両オネジ**  
—ロングストレート・オス—

Type: YCLPFP  
M材質: S35C  
S表面処理: 三価クロメート

型式 Type	No.	T R(PT)	F G(PF)	L	l1	l2	B	¥基準単価	
								YCLPFP	—
22F	1/4	1/4	74	16	19	1,040	—		
33F	3/8	3/8	80	18	22	1,250	—		
44F	1/2	1/2	95	20	27	1,380	—		

**PT・PF両オネジ**  
—45°エルボ・オス—

Type: YCWFPF, YCWFPFS  
M材質: S35C, SUS304  
S表面処理: 三価クロメート

型式 Type	No.	T R(PT)	F G(PF)	L1	L2	l1	l2	¥基準単価	
								YCWFPF	YCWFPFS
11F	1/8	1/8	19	19	12	13	560	1,630	
22F	1/4	1/4	20	22	13	16	570	1,630	
33F	3/8	3/8	23	26	15	18	610	1,740	
44F	1/2	1/2	28	29	18	20	720	2,420	

**PT・PTねじ**  
—エルボ—

Type: YCLPT, YCLPTS  
M材質: S25C, SUS304  
S表面処理: 三価クロメート

型式 Type	No.	T1 R(PT)	T2 R(PT)	L1	L2	l1	l2	¥基準単価	
								YCLPT	YCLPTS
11	1/8	1/8	20	20	13	13	400	1,100	
12	1/8	1/4	20	24	13	16	600	—	
13	1/8	3/8	20	27	13	17	700	—	
22	1/4	1/4	24	24	16	16	700	1,150	
23	1/4	3/8	24	27	16	17	800	—	
33	3/8	3/8	27	27	17	17	850	1,650	
34	3/8	1/2	30	30	17	18	970	—	
44	1/2	1/2	30	30	19	19	1,050	—	
66	3/4	3/4	36	36	23	23	1,180	—	

**PT・PFオス**  
—エルボ・オス—

Type: YCLPFP, YCLPFPFS  
M材質: S25C, SUS304  
S表面処理: 三価クロメート

型式 Type	No.	T R(PT)	F G(PF)	L1	L2	l1	l2	¥基準単価	
								YCLPFP	YCLPFPFS
11F	1/8	1/8	21	20	14	13	300	1,400	
12F	1/8	1/4	22	24	14	16	400	2,900	
21F	1/4	1/8	22	21	15	13	600	2,900	
22F	1/4	1/4	25	24	17	16	610	1,400	
23F	1/4	3/8	27	27.5	17	17.5	620	2,900	
32F	3/8	1/4	30	26	20	16	630	3,000	
33F	3/8	3/8	30	27.5	20	17.5	630	1,600	
34F	3/8	1/2	32	32	20	20	770	3,570	
44F	1/2	1/2	36	32	24	20	780	2,160	
46F	1/2	3/4	38	36	24	22	1,080	5,890	
64F	3/4	1/2	42	34	28	20	1,180	6,340	
66F	3/4	3/4	43	37	28	22	1,250	3,840	

仕様 使用流体 油・水  
最高使用圧力 20.6MPa(210kg/cm<sup>2</sup>以下)

**PT・PF両オネジ**  
—45°エルボ・メス—

Type: YCWPF, YCWPFSS  
M材質: S25C, SUS304  
S表面処理: 三価クロメート

型式 Type	No.	T R(PT)	F G(PF)	L1	L2	l1	l2	¥基準単価	
								YCWPF	YCWPFSS
11F	1/8	1/8	18	17	12	11	560	1,630	
22F	1/4	1/4	21	21	13	13	570	1,630	
33F	3/8	3/8	23	23	15	15	610	1,740	
44F	1/2	1/2	29	28	18	18	720	2,420	

**PT・PT両オネジ**  
—45°エルボ—

Type: YCWPT  
M材質: S25C  
S表面処理: 三価クロメート

型式 Type	No.	T1 R(PT)	T2 R(PT)	L	l	¥基準単価	
						YCWPT	—
11	1/8	1/8	17	12	12	650	—
22	1/4	1/4	19	14	14	670	—
33	3/8	3/8	22	15	15	750	—
44	1/2	1/2	28	18	18	840	—

**PT・PFメス**  
—エルボ・メス—

Type: YCLPF, YCLPFS  
M材質: S25C, SUS304  
S表面処理: 三価クロメート

型式 Type	No.	T R(PT)	F G(PF)	L1	L2	l1	l2	¥基準単価	
								YCLPF	YCLPFS
11F	1/8	1/8	21	18	14	11	300	1,400	
12F	1/8								