

六角穴付ボルト

—三価クロメート—

CADデータフォルダ名: 35_Screws

RoHS

CBE

材質 SCM435
表面処理 三価クロメート
硬度 HRC32~39
※強度区分 10.9

M×P	A	E	B
2×0.4	3.8	2	1.5
2.6×0.45	4.5	2.6	2
3×0.5	5.5	3	2.5
4×0.7	7	4	3
5×0.8	8.5	5	4
6×1.0	10	6	5
8×1.25	13	8	6
10×1.5	16	10	8
12×1.75	18	12	10

※強度区分とは、ネジの引張強さです。

(例) 10.9
降伏点または耐力の最小値が引張強さの90%であることを示します。
引張強さの最小値が1040N/mm²であることを示します。

参考: 六角穴付ボルトに対するザグリ及びボルト穴の寸法 P.1777

型式	ℓ	¥基準単価				¥スライド単価			
		1~9本	10~19本	20~49本	50本以上	1~9本	10~19本	20~49本	50本以上
CBE 2-5	5	120	72	48	30				
6	6	120	72	48	30				
8	8	120	72	48	30				
10	10	120	72	48	30				
CBE 2.6-5	5	110	61	44	30				
6	6	110	61	44	30				
8	8	120	66	48	30				
10	10	120	66	48	30				
CBE 3-4	4	79	55	32	25				
5	5	69	31	28	22				
6	6	69	31	28	19				
8	8	69	31	28	19				
10	10	74	33	30	22				
12	12	74	33	30	22				
15	15	74	33	30	22				
18	18	74	33	30	22				
20	20	74	33	30	22				
25	25	77	35	31	24				
30	30	82	37	33	28				
35	35	82	45	33	28				
CBE 4-5	5	84	46	34	25				
6	6	74	33	30	22				
8	8	74	33	30	22				
10	10	74	33	30	22				
12	12	79	36	32	22				
15	15	79	36	32	24				
18	18	79	36	32	24				
20	20	79	36	32	24				
25	25	79	36	32	24				
30	30	84	38	34	31				
35	35	87	39	35	33				
40	40	94	42	40	39				
45	45	94	42	40	39				
50	50	94	42	40	39				
CBE 5-6	6	94	42	38	25				
8	8	74	33	30	22				
10	10	74	33	30	22				
12	12	74	33	30	22				

型式	ℓ	¥基準単価				¥スライド単価			
		1~9本	10~19本	20~49本	50本以上	1~9本	10~19本	20~49本	50本以上
CBE 5-15	15	74	33	30	24				
18	18	79	36	32	28				
20	20	79	36	32	28				
25	25	79	36	32	28				
30	30	87	39	35	33				
35	35	94	42	41	39				
40	40	99	45	44	43				
45	45	100	49	48	47				
50	50	105	53	52	51				
CBE 6-8	8	89	40	36	24				
10	10	74	33	30	24				
12	12	74	33	30	24				
15	15	74	33	30	24				
18	18	79	36	32	28				
20	20	79	36	32	28				
25	25	79	36	32	28				
30	30	87	39	35	33				
35	35	94	42	41	39				
40	40	99	45	44	43				
45	45	105	52	51	50				
50	50	110	56	55	54				
55	55	110	56	55	54				
60	60	145	65	58	54				
65	65	155	70	62	54				
70	70	165	74	66	60				
75	75	200	90	80	70				
CBE 8-10	10	110	54	53	52				
12	12	94	42	41	39				
15	15	94	42	41	39				
18	18	94	42	41	39				
20	20	94	42	41	39				
25	25	99	45	44	43				
30	30	99	45	44	43				
35	35	110	57	56	55				
40	40	115	63	62	61				
45	45	115	67	66	65				
50	50	125	89	88	87				
55	55	125	110	109	108				

Order 注文例

型式 CBE4-10

Delivery 出荷日

在庫品 翌日出荷 P.89

ご希望によりPM5:00迄、当日出荷受付致します。

六角穴付ボルト(パック販売)/六角穴付ボルト

—三価クロメート/ユニクロメッキ—



CADデータフォルダ名: 35_Screws

RoHS

PACK-SCBE

材質 SCM435
表面処理 三価クロメート
硬度 HRC32~39
※強度区分 10.9

CBM

※CBMはRoHS非対応

材質 SCM435
表面処理 ユニクロメッキ
硬度 HRC32~39
※強度区分 10.9

型式	ℓ	PACK-SCBE		型式	ℓ	PACK-SCBE	
		¥基準単価	¥スライド単価			¥基準単価	¥スライド単価
PACK-SCBE 2-5	5	1,500	900	PACK-SCBE 6-8	8	1,190	710
6	6			10	10		
8	8			12	12		
10	10			15	15		
PACK-SCBE 2.6-5	5	1,480	880	20	20	1,370	820
6	6			25	25	1,610	960
8	8			30	30	1,910	1,140
10	10			40	40	2,130	1,260
PACK-SCBE 3-5	5	1,100	680	45	45	2,480	1,470
6	6	940	560	50	50	2,690	1,600
8	8			60	60	2,690	1,600
10	10			PACK-SCBE 50本/パック			
12	12	1,100	680	PACK-SCBE 8-12	8	1,950	1,180
15	15			15	15		
20	20			20	20		
25	25			25	25		
30	30			30	30		
35	35			35	35		
PACK-SCBE 4-6	6	1,100	680	40	40	2,710	1,660
8	8			45	45	3,020	1,830
10	10			50	50	3,230	1,960
12	12			55	55	4,330	2,610
15	15			60	60	5,400	3,260
20	20			PACK-SCBE 50本/パック			
25	25			PACK-SCBE 10-15	10	1,300	780
30	30			20	20		
35	35			25	25		
40	40			30	30		
45	45			35	35		
PACK-SCBE 5-8	8	1,100	680	40	40	1,440	860
10	10			45	45	1,480	880
12	12			50	50	1,600	960
15	15			55	55	1,740	1,000
20	20			60	60	1,740	1,000
25	25			PACK-SCBE 20本/パック			
30	30			PACK-SCBE 12-15	12	1,500	900
35	35			20	20		
40	40			25	25		
45	45			30	30		
50	50			35	35		
55	55			40	40		
60	60			45	45		
				50	50		
				55	55		
				60	60		

*ℓ部はJIS B 1176(2000)に基づきます。

Order 注文例

型式 PACK-SCBE6-10 CBM8-20

Delivery 出荷日

在庫品 翌日出荷 P.89

ご希望によりPM5:00迄、当日出荷受付致します。

PACK-SCBEはパック販売、CBMは単品販売となります。
パック販売品は注文数量1で1パック納入されます。

型式	ℓ	パラチャージ		型式	ℓ	パラチャージ	
		¥基準単価	¥スライド単価			¥基準単価	¥スライド単価
CBM 3-6	6	15	5	CBM 8-12	12	40	25
8	8			15	15		
10	10			20	20		
12	12			25	25		
15	15			30	30		
20	20			35	35		
25	25			40	40		
30	30			45	45		
35	35			50	50		
CBM 4-6	6	19	7	CBM 10-15	10	61	24
8	8			15	15		
10	10			20	20		
12	12			25	25		
15	15			30	30		
20	20			35	35		
25	25			40	40		
30	30			45	45		
35	35			50	50		
CBM 5-8	8	21	8	CBM 12-15	12	101	40
10	10			15	15		
12	12			20	20		
15	15			25	25		
20	20			30	30		
25	25			35	35		
30	30			40	40		
35	35			45	45		
40	40			50	50		
45	45			55	55		
50	50			60	60		
CBM 6-8	8	23	9	CBM 15-20	15	120	47
10	10			20	20		
12	12			25	25		
15	15			30	30		
20	20			35	35		
25	25			40	40		
30	30			45	45		
35	35			50	50		
40	40			55	55		
45	45			60	60		

※部 1~14本のご注文は基準単価+パラチャージを申し受けます。
[計算例] CBM3-6 を2本ご注文の場合
(基準単価15円+パラチャージ50円)×2本=130円
※ℓ部はJIS B 1176(2000)に基づきます。

35
ナット・座金