

L型表面処理アングル

一面切削直角度外側基準フリー指定タイプ



類似寸法は加工部品Cナビ <http://cp.misumi.jp/10-013/>

RoHS

アングルは商品に穴が無いので、SS材は針金で、アルミ材はアルミ針金で商品を縛り、つるしてメッキ処理します。
処理後下記のように針金で縛った箇所のみ変色する場合があります。

	T	A	B	L
L ~300	±0.3	±0.5	±0.5	±0.5
L 301~	±0.5	±0.7	±0.7	±0.5

材質	表面処理	Code	直角度k				
			T寸法	A・B寸法の長手	L~300	L301~400	L401~500
SS400	四三酸化鉄皮膜	BLAS	5・6	最小~ 75	0.05	-	-
	無電解ニッケルメッキ	MLAS		最小~ 50	0.05	0.2	0.25
	ユニクロメッキ	YLAS		51~ 80	0.1	0.25	0.35
	三価クロメート	SLAS		81~125	0.1	0.3	0.4
A6063	アルマイト(白色)	WLAA	12・15	最小~ 80	0.05	0.3	0.35
	アルマイト(黒色)	ELAA		81~125	0.1	0.35	0.4

Type	型式	指定1mm単位			
		T	A	B	L
BLAS MLAS YLAS SLAS	5	20~75	20~75	25~300	
	6	25~125	25~125		
	10				
	12				
	15				50~150
WLAA ELAA	5	20~75	20~75	25~300	
	6	25~100	25~100		
	10				
	12				50~125

Order 注文例

型式 - A - B - L

BLAS10 - A75 - B50 - L100

Delivery 出荷日

● BLAS・MLAS 3 日目発送

● YLAS・SLAS・WLAA・ELAA 5 日目発送

Price 価格

■数量スライド価格 (1円未満切り捨て) P89

数量	1~9	10~19	20~49
値引率	基準単価	5%	10%

◎表示数量超えはお見積り

Alteration 追加加工

型式 - A - B - L - (CKC・CCA・CCB...etc.)

BLAS10 - A120 - B120 - L150 - CKC

Alteration	Code	Spec.	¥/1Code
任意のコーナーをカットすることができます。 1≤コーナーカット≤30 1mm単位指定	CCA CCB CCC CCD	指定1mm ¥/1Code	800
指定方法			
(例)AとDのコーナーをC5でカットする場合 →CCA5~CCD5			

型式	T	A	B	Y基準単価						
				最短L~50	L51~100	L101~150	L151~200	L201~250	L251~300	
BLAS (SS400四三酸化鉄皮膜)	5	20~50	20~50	1.810	2.830	4.040	5.280	6.590	7.870	
				2.210	3.850	5.460	6.770	8.100	9.400	
				2.400	4.130	5.820	7.570	9.330	10.970	
	6	51~75	25~50	2.040	3.560	5.090	6.650	8.200	9.870	
				2.540	4.440	6.360	8.770	10.280	12.080	
				2.660	4.600	6.550	8.530	10.540	12.400	
	10	76~100	101~125	3.080	5.370	7.650	10.000	12.330	14.540	
				3.230	5.510	7.870	10.300	12.730	14.960	
				3.500	6.080	8.680	10.880	14.050	16.540	
	MLAS (SS400無電解ニッケルメッキ)	5	20~50	20~50	1.810	2.830	4.040	5.280	6.590	7.870
					2.210	3.850	5.460	6.770	8.100	9.400
					2.400	4.130	5.820	7.570	9.330	10.970
6		51~75	25~50	2.040	3.560	5.090	6.650	8.200	9.870	
				2.540	4.440	6.360	8.770	10.280	12.080	
				2.660	4.600	6.550	8.530	10.540	12.400	
10		76~100	101~125	3.080	5.370	7.650	10.000	12.330	14.540	
				3.230	5.510	7.870	10.300	12.730	14.960	
				3.500	6.080	8.680	10.880	14.050	16.540	

型式	T	A	B	Y基準単価						
				最短L~50	L51~100	L101~150	L151~200	L201~250	L251~300	
YLAS (SS400ユニクロメッキ)	5	20~50	20~50	1.740	3.050	4.330	5.670	6.980	8.240	
				2.370	4.120	5.820	7.600	9.370	11.040	
				2.180	3.810	5.410	7.070	8.730	10.310	
	6	51~75	25~50	2.880	4.410	6.190	8.030	9.940	11.700	
				2.180	3.790	5.400	7.070	8.730	10.290	
				2.710	4.700	6.720	9.270	10.890	12.800	
	10	76~100	101~125	2.850	4.870	6.890	8.980	11.120	13.090	
				3.290	5.650	8.020	10.510	12.970	15.300	
				2.680	4.670	6.660	8.730	10.780	12.690	
	SLAS (SS400三価クロメート)	5	20~50	20~50	1.740	3.050	4.330	5.670	6.980	8.240
					2.370	4.120	5.820	7.600	9.370	11.040
					2.180	3.810	5.410	7.070	8.730	10.310
6		51~75	25~50	2.880	4.410	6.190	8.030	9.940	11.700	
				2.180	3.790	5.400	7.070	8.730	10.290	
				2.710	4.700	6.720	9.270	10.890	12.800	
10		76~100	101~125	2.850	4.870	6.890	8.980	11.120	13.090	
				3.290	5.650	8.020	10.510	12.970	15.300	
				2.680	4.670	6.660	8.730	10.780	12.690	

型式	T	A	B	Y基準単価						
				最短L~50	L51~100	L101~150	L151~200	L201~250	L251~300	
WLAA (A6063白アルマイト)	5	20~50	20~50	2.140	3.700	5.200	6.830	8.430	9.980	
				2.360	4.550	6.400	8.410	10.400	12.310	
				3.110	5.230	7.280	9.520	11.780	13.890	
	6	51~75	25~50	2.620	4.480	6.340	8.330	10.300	12.160	
				3.210	5.480	7.790	10.790	13.100	14.960	
				3.400	5.660	7.920	10.350	12.860	15.160	
	10	76~100	101~125	3.910	6.510	9.130	12.010	14.870	17.580	
				4.180	6.450	9.160	12.160	15.000	17.840	
				3.700	6.230	8.780	11.540	14.320	16.890	
	ELAA (A6063黒アルマイト)	5	20~50	20~50	2.140	3.700	5.200	6.830	8.430	9.980
					2.360	4.550	6.400	8.410	10.400	12.310
					3.110	5.230	7.280	9.520	11.780	13.890
6		51~75	25~50	2.620	4.480	6.340	8.330	10.300	12.160	
				3.210	5.480	7.790	10.790	13.100	14.960	
				3.400	5.660	7.920	10.350	12.860	15.160	
10		76~100	101~125	3.910	6.510	9.130	12.010	14.870	17.580	
				4.180	6.450	9.160	12.160	15.000	17.840	
				3.700	6.230	8.780	11.540	14.320	16.890	

型式	T	A	B	Y基準単価						
				最短L~50	L51~100	L101~150	L151~200	L201~250	L251~300	
WLAA (A6063白アルマイト)	5	20~50	20~50	1.770	3.030	4.300	5.640	6.970	8.210	
				2.240	3.840	5.410	7.060	8.730	10.280	
				2.140	3.640	5.160	6.750	8.240	9.830	
	6	51~75	25~50	2.500	4.180	5.880	7.680	9.470	11.180	
				2.220	3.880	5.540	7.240	8.980	10.600	
				2.670	4.600	6.560	8.620	10.690	12.590	
	10	76~100	101~125	2.790	4.740	6.700	8.770	10.840	12.780	
				2.580	4.440	6.340	8.320	10.310	12.160	
				3.090	5.430	7.740	10.210	12.680	14.970	
	ELAA (A6063黒アルマイト)	5	20~50	20~50	1.880	3.210	4.550	5.980	7.390	8.710
					2.370	4.050	5.680	7.440	9.200	10.840
					2.260	3.840	5.430	7.110	8.790	10.360
6		51~75	25~50	2.650	4.420	6.190	8.090	9.970	11.790	
				2.350	4.090	5.830	7.630	9.480	11.190	
				2.810	4.820	6.680	9.020	11.200	13.190	
10		76~100	101~125	3.170	5.200	7.240	9.480	11.740	13.860	
				2.720	4.640	6.620	8.700	10.800	12.750	
				3.260	5.700	8.100	10.700	13.310	15.740	

58
形鋼材
アングル