



Alterations 追加加工  
型式 - L - P - W - N - (AKC・AWC...etc.)  
ERDF2 - 150.00 - P1.00 - W0.60 - N80 - AKC 90

Alterations	Code	Spec.	¥/Code
	AKC	AKC=指定1°単位 0 ≤ AKC < 360	200
	AWC	AWC=指定1°単位 0 ≤ AWC < 360	300
	ARC	ARC=指定1°単位 0 ≤ ARC < 360	300
	ADC	ADC=指定1°単位 0 ≤ ADC < 360	400
	KGA	KGA=指定1°単位 0 < KGA < 360	300
	KGD	KGD=指定1°単位 0 < KGD < 360	300
	HC	HC=指定0.1mm単位 D+1 ≤ HC < H	200

追加加工詳細 P.199

Alterations	Code	Spec.	¥/Code
	HCC	HCC=指定0.1mm単位 D+1 ≤ HCC < H-0.3	400
	TC	TC=指定0.1mm単位 T/2 ≤ TC < T (L,N寸法は指定寸法通り) T-TC ≤ Lmax.-L	200
	NHC	ツバ裏部ナンバリング 指定範囲・指定方法は P.200	(1・2文字) 50 (3文字) 100
	NHN	ツバ裏部ナンバリング(自動連番) 指定範囲・指定方法は P.200	(1・2文字) 50 (3文字) 100
	TMC	先端面LAP仕上 W ≥ 0.6に適用	1,000
	MC	抜きタップ加工 D8・9 → M4 D10 → M5 D12 → M6 ERDPJ,ERDFJ D ≥ 8に適用 TMCのみ併用可	300

■ノーマルタイプ

ツバ厚4mm		ツバ厚JIS		型式 Type	D	指定0.01mm単位		N 指定1mm単位
H	T	H	T			L	W	
3	4	3	4	ERDP (T4) ERDPJ (JIS)	1.5	50.00~200.00	0.75~ 1.40	N ≥ 30 20 ≤ (L-N) ≤ 150
4		2			50.00~250.00	1.00~ 1.90		
5		2.5			50.00~300.00	1.25~ 2.40		
6		3				1.50~ 2.90		
7		3.5				1.75~ 3.40		
8		4				2.00~ 3.90		
9		4.5				2.25~ 4.40		
10		5				2.50~ 4.90		
11		5.5			50.00~350.00	2.75~ 5.40	N ≥ 30 20 ≤ (L-N) ≤ 200	
12		6				3.00~ 5.90		
13		6.5				3.25~ 6.40		
14		7				3.50~ 6.90		
15		8		4.00~ 7.90				
16		9		4.50~ 8.90				
17		10		5.00~ 9.90				
		11		6.00~ 11.90				

■ステップタイプ

ツバ厚4mm		ツバ厚JIS		型式 Type	D	指定0.01mm単位		N 指定1mm単位
H	T	H	T			L	P	
3	4	3	4	ERDF (T4) ERDFJ (JIS)	1.5	50.00~200.00	0.60~ 1.40	N ≥ 30 20 ≤ (L-N) ≤ 150
4		2			50.00~250.00	0.80~ 1.90		
5		2.5			50.00~300.00	1.00~ 2.40		
6		3				1.50~ 3.40		
7		3.5				2.00~ 3.90		
8		4				2.50~ 4.40		
9		4.5				3.00~ 4.90		
10		5				3.50~ 5.40		
11		5.5			50.00~350.00	4.00~ 5.90	P/2 ≤ W ≤ (P-0.1) N ≥ 30 20 ≤ (L-N) ≤ 200	
12		6				4.50~ 6.40		
13		7				5.00~ 6.90		
14		8				6.00~ 7.90		
15		9		6.90~ 8.90				
16		10		7.90~ 9.90				
17		11		8.90~ 11.90				

Order 注文例  
型式 - L - P - W - N  
(ノーマルタイプ) ERDP5 - 145.05 - W3.20 - N95  
(ステップタイプ) ERDF2 - 150.00 - P1.00 - W0.60 - N80

Delivery 出荷日  
3 日目発送

Price 価格  
■数量スライド価格 (1円未満切り捨て) P.47  
数量 1~4 5~12 13~49 50~100 表示数量超えは  
値引率 基準単価 5% 10% 15% 価格・出荷日見積り

■ノーマルタイプ ERDP ERDPJ

型式 Type	D	¥基準単価 1~4本			
		L50.00 ~200.00	L200.01 ~250.00	L2 50.01 ~300.00	L300.01 ~350.00
ERDP ERDPJ	1.5	1,310	-	-	-
	2	1,170	1,480	-	-
	2.5	1,170	1,480	1,700	-
	3				
	3.5				
	4	1,290	1,570	1,800	-
	4.5	1,340	1,630	1,880	2,140
	5	1,410	1,720	1,980	2,180
	5.5	1,510	1,820	2,110	2,420
	6	1,560	1,870	2,130	2,470
	6.5	1,780	2,130	2,370	2,580
	7	1,890	2,260	2,510	2,750
12	2,270	2,710	3,010	3,290	

■ステップタイプ ERDF ERDFJ

型式 Type	D	¥基準単価 1~4本			
		L50.00 ~200.00	L200.01 ~250.00	L250.01 ~300.00	L300.01 ~350.00
ERDF ERDFJ	1.5	1,450	-	-	-
	2	1,300	1,640	-	-
	2.5	1,300	1,640	1,880	-
	3				
	3.5				
	4	1,430	1,740	2,000	-
	4.5	1,490	1,810	2,090	2,380
	5	1,570	1,910	2,200	2,430
	5.5	1,670	2,020	2,340	2,690
	6	1,730	2,080	2,360	2,750
	6.5	1,980	2,350	2,800	3,060
	7	2,100	2,510	2,790	3,060
12	2,520	3,010	3,350	3,660	