

溝無しガイドレール

—L寸指定タイプ(油溝なし・油溝付)—

追加加工価格も数量スライド適用 P.49

■取付ボルト穴2ヶ所 [2H]

■取付ボルト穴3ヶ所 [3H]

■取付ボルト穴4ヶ所 [4H]

■ボルト穴サイズ表

W	T	d1	d2	t1	ω
10	10・12.5・15	8	4.5	5	4.5
12.5	10・15・20				5
15	10・15・20・25				6
20	15・20	11	6.5	7	9
25	25・30				9
25	20・25・30・35	17	11.5	11	10
30	25・30・35				11
35	30・35				13
40	30・40	19	12.5	13	13

■油溝詳細 (GRSFM-□H・GRMFM-□H)

指示のない角部はC≦1となります。

■油溝ピッチ早見表

T	P
10	8
12.5	13
15	18
20	28
25	38
30	48
35	58
40	68

① L≦P+10の時、油溝が1サイクル (1ピッチ)分、切れない場合がありますのでご注意ください。

■油溝ピッチ算出方法
P=(T-6)×2

Order 注文例

型式 - T - L - A - B - C - D

[2H] GRSF-2H10 - 10 - 75 - A6 - B16 - C - D

[3H] GRSF-3H10 - 10 - 100 - A6 - B16 - C26

[4H] GRSF-4H10 - 10 - 100 - A6 - B16 - C26 - D36

Delivery 出荷日

- GRSF-□H 5 日目発送
- GRSFM-□H 5 日目発送
- GRMF-□H 5 日目発送
- GRMFM-□H 5 日目発送

① 同一サイズ3本以上は一律810円

Price 価格

数量スライド価格 (①1円未満切り捨て) P.47

数量	1~9	10~19	20~30	表示数量超えは
値引率	基準単価	5%	10%	価格・出荷日お見積り

油溝なし

W	T	¥基準単価 1~9本															
		L35~55		L60~75		L80~95		L100~115		L120~135		L140~150		L155~180		L185~200	
		GRSF	GRMF	GRSF	GRMF	GRSF	GRMF	GRSF	GRMF	GRSF	GRMF	GRSF	GRMF	GRSF	GRMF	GRSF	GRMF
10	10	3,110	3,050	3,430	3,370	3,770	3,590	4,170	3,820								
10	12.5	3,210	3,140	3,530	3,460	3,850	4,290	4,870	3,820								
10	15	3,280	3,230	3,640	3,570	3,960	3,890	4,430	3,940								
12.5	10	3,350	3,010	3,710	3,340	4,070	3,660	4,430	3,990								
12.5	15	3,350	3,010	3,710	3,340	4,070	3,660	4,430	3,990								
12.5	20	3,590	3,230	3,950	3,560	4,350	3,910	4,790	4,310								
15	10	3,350	3,010	3,710	3,340	4,070	3,660	4,430	3,990	4,870	4,390	5,360	4,830				
15	15	3,470	3,120	3,830	3,440	4,190	3,770	4,550	4,090	5,010	4,500	5,510	4,950				
15	20	3,710	3,350	4,070	3,670	4,430	3,990	4,790	4,310	5,270	4,740	5,800	5,210				
15	25	3,830	3,440	4,220	3,790	4,640	4,170	5,100	4,590	5,610	5,050	5,830	5,250				
20	10	3,830	3,440	4,190	3,770	4,550	4,090	4,910	4,420	5,270	4,740	5,390	4,860	5,930	5,350	6,520	5,880
20	15	4,070	3,660	4,430	3,990	4,790	4,310	5,150	4,640	5,510	4,960	5,630	5,070	6,200	5,580	6,820	6,150
20	25	4,310	3,880	4,670	4,210	5,030	4,530	5,390	4,860	5,750	5,180	5,870	5,290	6,460	5,820	7,110	6,400
20	30	4,400	4,340	4,810	4,520	5,020	4,710	5,560	5,250	5,970	5,220	6,410	5,610	7,050	6,170	7,750	6,790
20	40	4,530	4,430	4,720	4,600	5,190	4,780	5,660	5,300	6,150	5,500	6,600	5,670	7,260	6,230	7,990	6,850
25	10	4,650	4,580	4,880	4,770	5,290	4,970	5,850	5,530	6,280	5,740	6,730	5,930	7,410	6,520	8,150	7,170
25	15	4,890	4,800	5,100	4,990	5,510	5,190	6,070	5,750	6,500	5,960	6,950	6,150	7,630	6,740	8,370	7,390
25	20	5,130	5,040	5,340	5,230	5,750	5,430	6,310	5,990	6,740	6,200	7,190	6,390	7,870	6,980	8,600	7,620
25	25	5,130	5,040	5,340	5,230	5,750	5,430	6,310	5,990	6,740	6,200	7,190	6,390	7,870	6,980	8,600	7,620
25	30	5,210	5,140	5,480	5,350	5,760	5,590	6,440	6,230	7,350	6,460	7,350	6,650	8,150	7,350	8,460	7,580
25	35																

① 同一サイズ3本以上は一律810円

油溝付

W	T	¥基準単価 1~9本															
		L50~65		L70~85		L90~105		L110~125		L130~145		L150~165		L170~185		L190~200	
		GRSF	GRMF	GRSF	GRMF	GRSF	GRMF	GRSF	GRMF	GRSF	GRMF	GRSF	GRMF	GRSF	GRMF	GRSF	GRMF
30	25	5,270	4,740	5,630	5,070	5,990	5,390	6,350	5,720	6,830	6,150	7,430	6,680	8,980	8,090	10,780	9,700
30	30	5,750	5,180	6,110	5,510	6,470	5,830	6,830	6,150	7,310	6,580	7,910	7,110	9,460	8,520	11,260	10,140
30	35	5,880	5,770	6,420	6,280	6,960	6,780	7,410	6,890	7,990	7,420	8,540	7,980	9,720	9,080	11,830	10,730
35	25																
35	30																
35	35																
40	30	6,830	6,150	7,190	6,470	7,550	6,790	7,910	7,110	8,380	7,540	8,980	8,080	10,540	9,490	12,340	11,110
40	40	7,430	6,680	7,790	7,010	8,140	7,320	8,500	7,650	8,980	8,080	9,580	8,620	11,140	10,030	12,940	11,640

型式	No. (ボルト穴)	W	T 選択	L 指定5mm単位	ボルト穴ピッチ 指定0.5mm単位							
					A		B		C		D	
Type					min.	max.	min.	max.	min.	max.	min.	max.
油溝なし	GRSF (SKS3)	10	10	[2H] *35・40~75	6	B-10	A+10	[2H] L-6	B+10	[3H] L-6	C+10	[4H] L-6
			12.5	[3H] 60~100				[4H] D-10				
			15	[4H] 100								
			12.5	10				[2H] *35・40~75				
				15				[3H] 60~100				
				20				[4H] 100				
	GRMF (HPM2T相当)	20	10	[2H] 40~75	7	B-11.5	A+11.5	[2H] L-7	B+11.5	[3H] L-7	C+11.5	[4H] L-7
			15	[3H] 60~150				[4H] D-11.5				
			20	[4H] 100~150								
			15	15				[2H] 40~150				
				20				[3H] 100~200				
				25				[4H] 155~200				
油溝付	GRSFM (SKS3)	20	15	[2H] 40~150	7.5	B-13	A+13	[2H] L-7.5	B+13	[3H] L-7.5	C+13	[4H] L-7.5
			20	[3H] 100~200				[4H] D-13				
			25	[4H] 155~200								
			30	20				[2H] 40~150				
				25				[3H] 100~200				
				30				[4H] 155~200				
	GRMFM (HPM2T相当)	30	25	[2H] 40~150	9	B-16	A+16	[2H] L-9	B+16	[3H] L-9	C+16	[4H] L-9
			30	[3H] 100~200				[4H] D-16				
			35	[4H] 155~200								
			25	20				[2H] 40~150				
				25				[3H] 100~200				
				30				[4H] 155~200				
*印のL35は油溝なし (GRSF・GRMF)のみ適用	GRSF (SKS3)	30	25	[2H] 50~165	10.5	B-19	A+19	[2H] L-10.5	B+19	[3H] L-10.5	C+19	[4H] L-10.5
			30	[3H] 110~200				[4H] D-19				
			35	[4H] 190~200								
			35	25				[2H] 50~165				
				30				[3H] 120~200				
				35				[4H] 190~200				
	GRMFM (HPM2T相当)	40	30	[2H] 50~165	10.5	B-21	A+21	[2H] L-10.5	B+21	[3H] L-10.5	C+21	[4H] L-10.5
			35	[3H] 110~200				[4H] D-21				
			40	[4H] 190~200								
			30	25				[2H] 50~165				
				30				[3H] 120~200				
				35				[4H] 190~200				

*印のL35は油溝なし (GRSF・GRMF)のみ適用

Alterations 追加加工

型式 - T - L - A - B - (BP・KP・MC・CC)

GRMF-2H10 - 10 - 75 - A6 - B36 - MC

5 日目発送

Alterations	Code	Spec.	¥/1Code
タップ穴加工	BP	タップ穴加工 詳細 P.803	BP4 BP5 600 BP6 BP8 800
ノック穴加工	KP	ノック穴加工 ①材質HPM2T相当に適用 詳細 P.803	T10~35 900 T40 1,200
タップ穴に変更	MC	タップ穴に変更 ①W10~25に適用 詳細 P.804	500
C面取り	CC	C面取り 詳細 P.804	CC5~9 900 CC11 CC13 1,000

数量スライド価格 (①1円未満切り捨て) P.47

数量	1~9	10~19	20~30	表示数量超えは
値引率	基準単価	5%	10%	価格・出荷日お見積り

油溝付

W	T	¥基準単価 1~9本															
		L40~55		L60~75		L80~95		L100~115		L120~135		L140~150		L155~180		L185~200	
		GRSFM	GRMFM	GRSFM	GRMFM	GRSFM	GRMFM	GRSFM	GRMFM	GRSFM	GRMFM	GRSFM	GRMFM	GRSFM	GRMFM	GRSFM	GRMFM
10	10	3,530	3,460	3,950	3,890	4,380	4,110	4,880	4,400								
10	12.5	3,620	3,550	4,040	3,970	4,460	4,190	5,000	4,530								
10	15	3,700	3,640	4,150	4,080	4,580	4,300	5,140	4,650								
12.5	10	3,760	3,420	4,220	3,850	4,680	4,270	5,140	4,700								
12.5	15	3,760	3,420	4,220	3,850	4,680	4,270	5,140	4,700								
12.5	20	4,000	3,640	4,460	4,070	4,960	4,530	5,500	5,020								
15	10	3,760	3,420	4,220	3,850	4,680	4,270	5,140	4,700	5,690	5,200	6,180	5,640				
15	15	3,880	3,540	4,340	3,960	4,800	4,380	5,260	4,800	5,820	5,310	6,320	5,760				
15	20	4,120	3,750	4,580	4,170	5,040	4,600	5,500	5,020	6,080	5,550	6,610	6,020				
15	25	4,240	3,860	4,720	4,300	5,250	4,780	5,810	5,300	6,420	5,860	6,650	6,060				
20	10	4,240	3,860	4,720	4,300	5,250	4,780	5,810	5,300	6,080	5,550	6,200	5,660	6,740	6,150	7,340	6,690
20	15	4,480	4,070	4,940	4,500	5,400	4,920	5,860	5,350	6,320	5,770	6,440	5,880	7,010	6,390	7,630	6,950
20	25	4,720	4,290	5,180	4,720	5,640	5,140	6,100	5,560	6,5							