

整数刃径8サイズは、即日出荷対応可能

HSS HAND REAMER

ハイス鋼ハンドリーマ

●右刃ストレート刃 0.1mm単位指定タイプ

刃径D	公差	刃径D	シャンク径d
0.5~3	+0.007 +0.002	0.5~1.2	2
3.1~6	+0.009 +0.004	1.3~2.9	3
6.1~10	+0.012 +0.006	3~	D
10.1~18	+0.015 +0.007		
18.1~30	+0.017 +0.008		

シャンク径d	公差
2~30	-0.02 -0.05

材質 **HSS**

型番 HRST

刃径 D	食付長 T	刃長 ℓ	全長 L	刃数	¥単価 1~4本
0.5	2.5	12	30	4	4,100
0.6	2.5	12	30	4	4,010
0.7	2.5	12	30	4	3,620
0.8	3	15	35	4	3,410
0.9	4	20	40	4	3,320
1	4	20	40	4	2,930
1.1	5	25	45	4	2,840
1.2	5	25	45	4	2,840
1.3	5	25	45	4	2,840
1.4	5	25	45	4	2,110
1.5	5	25	45	4	2,080
1.6	6	30	55	4	2,080
1.7	6	30	55	4	2,540
1.8	6	30	55	4	2,080
1.9	6	30	55	4	2,540
2	6	30	55	4	1,960
2.1	6	30	55	4	1,890
2.2	6	30	55	4	1,890
2.3	7	35	65	4	2,260
2.4	7	35	65	4	2,030
2.5	7	35	65	4	1,960
2.6	7	35	65	4	2,260
2.7	7	35	65	4	2,020
2.8	7	35	65	4	2,260
2.9	8	40	72	6	2,050
3	8	40	72	6	1,870
3.1	8	40	72	6	1,870
3.2	8	40	72	6	1,590
3.3	8	40	72	6	1,590
3.4	8	40	72	6	1,870
3.5	8	40	72	6	1,870
3.6	8	40	72	6	1,870
3.7	8	40	80	6	1,870
3.8	8	40	80	6	1,870
3.9	8	40	80	6	1,870
4	8	40	80	6	1,490
4.1	8	40	80	6	1,590
4.2	9	45	85	6	1,590
4.3	9	45	85	6	1,870
4.4	9	45	85	6	1,870
4.5	9	45	85	6	1,870
4.6	9	45	85	6	2,060
4.7	9	45	90	6	2,060
4.8	9	45	90	6	1,680
4.9	9	45	90	6	2,060
5	9	45	90	6	2,060
5.1	9	45	90	6	1,780
5.2	10	45	95	6	1,760
5.3	10	45	95	6	1,650
5.4	10	45	95	6	1,740
5.5	10	45	95	6	1,780
5.6	10	45	95	6	1,810
5.7	10	50	100	6	1,810
5.8	10	50	100	6	2,150
5.9	10	50	100	6	2,150
6	10	50	100	6	2,150
6.1	10	50	100	6	1,850
6.2	10	50	100	6	2,150
6.3	10	50	100	6	1,850
6.4	10	50	100	6	1,920
6.5	10	50	100	6	1,850
6.6	10	50	100	6	2,150
6.7	11	55	105	6	1,820
6.8	11	55	105	6	1,920
6.9	11	55	105	6	1,850
7	11	55	105	6	1,780
7.1	11	55	105	6	2,440
7.2	11	55	110	6	2,440
7.3	11	55	110	6	2,440
7.4	11	55	110	6	2,440
7.5	11	55	110	6	2,440
7.6	11	55	110	6	2,100
7.7	12	60	115	6	2,440
7.8	12	60	115	6	2,440

●右刃ストレート刃 0.01mm単位指定タイプ

刃径D	公差	刃径D	シャンク径d
0.51~30.05	+0.005 0	0.51~1.25	2
		1.26~2.99	3
		3.01~	D

シャンク径d	公差
2~30.05	-0.02 -0.05

材質 **HSS**

型番 HRST

刃径 D	食付長 T	刃長 ℓ	全長 L	刃数	¥単価 1~4本
0.51	2.5	12	30	4	4,900
0.61	2.5	12	30	4	4,800
0.71	3	15	35	4	4,400
0.76	3	15	35	4	4,400
0.81	4	20	40	4	4,200
0.88	4	20	40	4	4,200
0.91	4	20	40	4	4,000
1.01	5	25	45	4	3,500
1.06	5	25	45	4	3,500
1.11	5	25	45	4	2,970
1.21	5	25	45	4	3,500
1.26	5	25	45	4	3,500
1.31	5	25	45	4	3,500
1.41	5	25	45	4	3,500
1.51	6	30	55	4	3,000
1.56	6	30	55	4	3,000
1.61	6	30	55	4	3,000
1.71	6	30	55	4	3,000
1.76	6	30	55	4	3,000
1.81	6	30	55	4	3,000
1.86	6	30	55	4	3,000
1.91	6	30	55	4	3,000
2.01	6	30	55	4	2,900
2.11	6	30	55	4	2,900
2.21	7	35	60	4	2,600
2.26	7	35	60	4	2,600
2.31	7	35	60	4	2,600
2.41	7	35	60	4	2,600
2.51	7	35	60	4	2,600
2.61	7	35	60	4	2,600
2.71	7	35	60	4	2,600
2.81	7	35	60	4	2,600
2.86	7	35	60	4	2,600
2.91	7	35	60	4	2,600
3.01	8	40	72	6	2,030
3.11	8	40	72	6	2,030
3.21	8	40	72	6	2,300
3.31	8	40	72	6	2,300
3.41	8	40	72	6	2,300
3.51	8	40	72	6	2,300
3.61	8	40	72	6	2,300
3.71	8	40	72	6	2,300
3.81	8	40	72	6	2,300
3.91	8	40	72	6	2,030
4.01	8	40	72	6	2,300
4.11	9	45	85	6	2,300
4.21	9	45	85	6	2,300
4.31	9	45	85	6	2,300
4.41	9	45	85	6	2,300
4.51	9	45	85	6	2,500
4.61	9	45	85	6	2,500
4.71	9	45	85	6	2,500
4.81	9	45	85	6	2,500
4.91	9	45	85	6	2,500
5.01	9	45	85	6	2,500
5.11	10	45	95	6	2,500
5.21	10	45	95	6	2,500
5.31	10	45	95	6	2,500
5.41	10	45	95	6	2,500
5.51	10	45	95	6	2,600
5.61	10	45	95	6	2,600
5.71	10	45	95	6	2,600
5.81	10	45	95	6	2,600
5.91	10	45	95	6	2,180
6.01	10	45	95	6	2,320
6.11	10	45	95	6	2,600
6.21	10	45	95	6	2,600
6.31	10	45	95	6	2,600
6.41	10	45	95	6	2,600
6.51	10	45	95	6	2,600
6.61	10	45	95	6	2,600
6.71	10	45	95	6	2,600
6.81	10	45	95	6	2,600

超硬

ハイス

Order 注文例 **HRST - 10.1** 型番 刃径 (D)

Price 価格 **数量スライド価格** (●1円未満切捨て) 切削条件 **P.691**

数量	1~4	5~9	10~49	50~99	100~
値引率		5%	10%	15%	

●左記以外の商品 **3** 日目発送 **お見積り**

Delivery 出荷日 **在庫品** **P.12**

●ご希望によりPM5:00迄、当日出荷受付致します。

Order 注文例 **HRST - 10.01** 型番 刃径 (D)

Price 価格 **数量スライド価格** (●1円未満切捨て) 切削条件 **P.691**

数量	1~4	5~9	10~49	50~99	100~
値引率		5%	10%	15%	

●左記以外の商品 **3** 日目発送 **お見積り**

Delivery 出荷日 **3** 日目発送