

赤枠部に、記号※と注釈を追加

<1>

型式 Type	d	D	L 指定0.1mm単位	Ds	適用ベアリング	¥基準単価											
						CLBU・CLBP			CLBUB・CLBPB			CLBUM・CLBPM			CLBUS・CLBPS		
						L1.0~25.0	25.1~50.0	50.1~100.0	L1.0~25.0	25.1~50.0	50.1~100.0	L1.0~25.0	25.1~50.0	50.1~100.0	L1.0~25.0	25.1~50.0	50.1~100.0
内輪用 (マイナス公差) CLBU CLBUB CLBUM CLBUS  (プラス公差) CLBP CLBPB CLBPM CLBPS	3	5	1.0~50.0	4	673ZZ・693ZZ・623ZZ	310	370	—	370	420	—	390	450	—	390	510	—
	4	7		6	674ZZ※・694ZZ・624ZZ	370	410	—	420	460	—	450	500	—	460	550	—
	5	8		7	675ZZ※・695ZZ・625ZZ	410	450	—	460	500	—	460	500	—	500	600	—
	6	9		8	676ZZ・696ZZ・626ZZ	450	480	—	500	540	—	500	530	—	540	650	—
	8	10		9	678ZZ	—	—	—	550	590	—	500	550	—	—	—	—
	10	11		10	678ZZ・698ZZ・628ZZ	480	520	—	490	520	—	530	580	—	580	680	—
	10	12		11	6700ZZ	—	—	—	550	590	—	500	550	—	—	—	—
	10	13		12	6800ZZ	520	550	720	510	550	690	550	600	780	630	750	980
	10	14		13	6900ZZ・6000ZZ	530	590	760	550	590	770	500	550	720	570	690	900
	10	17		16	6200ZZ・6300ZZ	570	630	820	580	630	830	530	580	770	610	730	960
	12	15		14	6701ZZ・6801ZZ	570	630	820	580	630	830	520	560	760	610	730	960
	12	16		15	6901ZZ・6001ZZ	570	630	820	580	630	830	530	580	770	610	730	960
	12	18	17	6201ZZ・6301ZZ	590	660	850	590	650	840	550	600	780	630	750	980	
	12	18	17	6702ZZ・6802ZZ	590	660	850	590	650	840	550	600	780	630	750	980	
	15	18	17	6902ZZ・6002ZZ	590	660	850	590	650	840	550	600	780	630	750	980	
	15	19	18	6202ZZ	600	670	900	590	670	890	570	630	850	650	820	1,080	
	15	21	20	6302ZZ	—	—	—	670	740	980	650	720	950	—	—	—	
	15	23	22	6802ZZ	610	700	940	590	670	890	570	630	850	650	820	1,080	
	15	23	22	6903ZZ・6003ZZ	610	700	940	590	670	890	570	640	860	650	820	1,080	
	15	24	23	6203ZZ	660	730	990	610	720	920	580	660	870	700	860	1,140	
	15	26	25	6303ZZ	—	—	—	670	740	980	650	720	950	—	—	—	
	17	20	19	6804ZZ	610	730	960	590	670	890	580	670	870	660	860	1,100	
	17	23	22	6904ZZ	630	730	950	600	710	910	580	680	880	660	860	1,100	
	20	23	22	6004ZZ・6204ZZ	650	730	960	670	740	980	650	720	950	740	900	1,180	
	20	29	28	6304ZZ	—	—	—	700	780	1,040	670	750	1,000	—	—	—	
	20	29	28	6805ZZ	650	730	960	680	750	1,000	660	730	970	760	940	1,240	
	20	29	28	6905ZZ	670	760	1,000	700	780	1,040	670	750	1,000	760	940	1,240	
	25	31	30	6005ZZ	700	780	1,040	730	810	1,070	700	780	1,030	790	980	1,280	
	25	33	32	6205ZZ	700	780	1,040	730	810	1,070	700	780	1,030	790	980	1,280	
	25	36	35	6305ZZ	—	—	—	790	890	1,120	760	990	1,230	—	—	—	
	25	33	32	6806ZZ	720	830	1,080	730	840	1,090	710	790	1,050	810	1,040	1,360	
	25	35	34	6906ZZ	720	830	1,080	740	870	1,140	720	830	1,100	810	1,040	1,360	
	30	38	37	6006ZZ	730	870	1,110	760	900	1,150	730	860	1,110	830	1,080	1,380	
	30	40	39	6206ZZ	750	880	1,150	780	970	1,280	750	910	1,190	850	1,100	1,420	
	30	43	42	6306ZZ	—	—	—	850	1,020	1,230	940	1,120	1,350	—	—	—	
	35	38	37	6807ZZ	820	960	1,200	790	890	1,120	760	990	1,230	970	1,230	1,500	
	35	42	41	6907ZZ	870	1,050	1,250	790	950	1,130	870	1,050	1,250	1,030	1,300	1,550	
	35	44	43	6007ZZ・6207ZZ	920	1,100	1,320	830	980	1,190	910	1,080	1,310	1,090	1,360	1,630	
	35	46	45	6207ZZ	—	—	—	850	1,020	1,230	940	1,120	1,350	—	—	—	
	35	48	47	6307ZZ	—	—	—	890	1,060	1,280	980	1,160	1,400	—	—	—	
	40	43	42	6808ZZ	930	1,110	1,340	840	990	1,210	930	1,090	1,330	1,120	1,400	1,710	
	40	46	45	6908ZZ	950	1,120	1,380	850	1,020	1,230	940	1,120	1,350	1,120	1,400	1,710	
	40	49	48	6008ZZ・6208ZZ	1,010	1,200	1,460	890	1,060	1,280	980	1,160	1,400	1,200	1,480	1,810	
	40	52	51	6208ZZ	—	—	—	940	1,190	1,510	1,020	1,300	1,640	—	—	—	
	40	54	53	6308ZZ	—	—	—	1,070	1,380	1,730	1,180	1,520	1,880	—	—	—	
	45	53	52	6009ZZ	—	—	—	990	1,280	1,600	1,090	1,410	1,740	—	—	—	
	45	55	54	6209ZZ	—	—	—	1,100	1,420	1,780	1,210	1,570	1,930	—	—	—	
	45	56	55	6010ZZ	—	—	—	1,120	1,440	1,810	1,230	1,600	1,960	—	—	—	
	45	60	59	6210ZZ	—	—	—	1,210	1,560	1,950	1,330	1,730	2,120	—	—	—	

※L=3未満のとき、※部ベアリングは使用できません。

<2>

<訂正用>

<1>

674ZZ※・694ZZ・624ZZ
675ZZ※・695ZZ・625ZZ

<2>

※L=3未満のとき、※部ベアリングは使用できません。