

P.2-1181<規格表>

型式HOGFW、HOGFWK、HOGFWRのホース呼び内径1Sの両側かしめの基準単価¥30,520を¥30,440に訂正。

型式		ホース長さ 指定0.1m単位	L 左かしめ形状	R 右かしめ形状	¥基準単価		
Type	ホース 呼び内径				ホース単価/m	かしめプラス料金	
						片側かしめ	両側かしめ
HOFW (ホース単体のみ) HOFWK (片側かしめ) HOFWR (両側かしめ)	6	0.5 ~ 100.0	—	—	260	—	—
	9				450		
	12				530		
	15				780		
	19	0.5 ~ 50.0	LC	RC	920	15,260	30,520
	1S	0.6 ~ 50.0			1,400		
	1.5S	0.6 ~ 50.0			2,510		
	2S	0.6 ~ 40.0			3,890		
HOGFW (ホース単体のみ) HOGFWK (片側かしめ) HOGFWR (両側かしめ)	15	0.5 ~ 50.0	—	—	880	—	—
	19				1,070		
	1S	0.6 ~ 50.0	LC	RC	2,190	15,220	30,440
	1.5S	0.6 ~ 40.0			2,860	18,600	37,200
	2S				4,440	29,300	58,600

<訂正用>

30,440