

P. 1 -1869 スタンダードタイプ<規格表>

型式 40 の基準単価：12,270 → -に変更

型式		A	B	L	T	D1	F	G	b	C	S	H	Y	d	d1	MA	h	f	e	W	付属ボルト	¥基準単価				
Type	DH7																					CLSB	CLSM	CLSAM	CLSS	
CLSB CLSM CLSAM CLSS (D10~30)	10	$+0.015$	50	33	35	10	30	35	18	4.5	29	—	10	5	4.5	8	M4	22	15	20	2	M4-15 1本	3,990	4,860	3,970	7,540
	12	$+0.018$	52	35	35	10	32	37	20	4.5	29	—	11	5	4.5	8	M4	22	15	22	2	M4-15 1本	4,860	5,740	4,790	8,420
	15	0	58	40	39	12	35	40	24	5.5	32	—	12.5	6	5.5	10	M5	24	17	25	2	M5-20 2本	5,610	6,390	5,300	9,760
	16	0	58	40	39	12	35	40	24	5.5	32	—	12.5	6	5.5	10	M5	24	17	25	2	M5-20 2本	5,610	6,390	—	—
	20	$+0.021$	73	45	50	12	40	50	28	6.6	33.8	10.5	14	7	5.5	9.5	M5	27	25	30	2	M5-20 2本	5,710	6,450	5,480	9,880
	25	0	93	55	60	15	50	62	36	9	41.5	12	18	10	6.6	11	M6	34	28	35	2	M6-25 2本	6,520	7,320	6,840	12,050
	30	0	103	65	70	15	60	72	42	9	47	15	21	10	9	14	M8	38	34	45	2	M8-25 2本	7,600	8,520	8,410	14,040
	35	$+0.025$	108	70	80	15	65	75	45	11	55	16	24	10	9	14	M8	44	39	50	3	M8-25 2本	8,650	9,710	10,220	—
	40	0	118	75	90	18	70	78	55	11	64	17	26	13	9	14	M8	53	40	60	3	M8-30 2本	9,890	11,100	—	—
	50	0	138	90	110	18	85	95	60	14	77.5	21	32	16	11	17.5	M10	65	48	70	3	M10-35 2本	11,930	13,360	17,780	—

<訂正用>

