

P. 2-676 <規格表>

HCBST「締付時のばね座金・平座金の高さ」を一部変更

型式		M×P	A	E	B	C	D	締付時のばね座金・平座金の高さ(参考)	¥パック価格	¥1本あたりの価格		
Type	M-L-SET1 (500個パック)											
HCBST	5 - 12 16	SET1	5×0.8	8.5	5	4	8.5	10	2.3	7,850	15.7	
										8,570	17.1	
			6 - 15 20 25	6×1.0	10	6	5	11.5	12.5	3.1	10,620	21.3
											11,250	22.5
											11,875	23.8
											19,375	38.8
	8 - 20 24 29	8×1.25	13	8	6	14.5	17	3.6	20,625	41.3		
									21,875	43.8		

<貼り付け用>

型式		M×P	A	E	B	C	D	締付時のばね座金・平座金の高さ(参考)	¥パック価格	¥1本あたりの価格		
Type	M-L-SET1 (500個パック)											
HCBST	5 - 12 16	SET1	5×0.8	8.5	5	4	8.5	10	2.3	7,850	15.7	
										8,570	17.1	
			6 - 15 20 25	6×1.0	10	6	5	11.5	12.5	3.1	10,620	21.3
											11,250	22.5
											11,875	23.8
											19,375	38.8
	8 - 20 24 29	8×1.25	13	8	6	14.5	17	3.6	20,625	41.3		
									21,875	43.8		