

赤字文字部、数値・区切り位置を修正

Alterations				指定位置ザグリ穴あけ	
特長	Type	No.	掲載ページ	ザグリ	右から左
					XA~XE
4面溝	HFSB NFSB CAFB HFSYB	4030	P531	240	240
		4031	P532		240
		4032	P533		240
		4033	P534		240
		4034	P535		240
		4035	P536		480
		4036	P537		480
		4037	P538		480
		4038	P539		480
		4039	P540		480
3面溝 1面フラット	HFPFB HFPFB	4040	P531	240	240
		4041	P532		240
2面溝 2面フラット	HFSTB HFSTB	4042	P531	240	240
		4043	P532		240
対面2面溝	HFSHB HFSHB	4044	P531	240	240
		4045	P532		240
1面溝3面フラット	HFSCB HFSCB	4046	P531	240	240
		4047	P532		240
角度付	HFSAB HFSAB	4048	P531	240	240
		4049	P532		240
黒アルマイト	HFSBB HFSBB	4050	P531	240	240
		4051	P532		240
曲面	HFSRB HFSRB	4052	P531	240	240
		4053	P532		240

Alterations				指定位置ザグリ穴あけ	
特長	Type	No.	掲載ページ	ザグリ	右から左
					XA~XE
4面溝	HFSB NFSB CAFB HFSYB	4030	P527	250	250
		4031	P528		250
		4032	P529		250
		4033	P530		250
		4034	P531		250
		4035	P532		500
		4036	P533		500
		4037	P534		500
		4038	P535		500
		4039	P536		500
3面溝 1面フラット	HFPFB HFPFB	4040	P527	250	250
		4041	P528		250
2面溝 2面フラット	HFSTB HFSTB	4042	P527	250	250
		4043	P528		250
対面2面溝	HFSHB HFSHB	4044	P527	250	250
		4045	P528		250
1面溝3面フラット	HFSCB HFSCB	4046	P527	250	250
		4047	P528		250
角度付	HFSAB HFSAB	4048	P527	250	250
		4049	P528		250
黒アルマイト	HFSBB HFSBB	4050	P527	250	250
		4051	P528		250
曲面	HFSRB HFSRB	4052	P527	250	250
		4053	P528		250

<貼り付け用>

Alterations				ザグリ	指定位置ザグリ穴あけ	
特長	Type	No.	掲載ページ		上から下	右から左
					XA~XE	YA~YE
4面溝	HFSB GFSB EFSB NFSB CAFB HFSYB	4010	P587	260	250	
		4080	P589		500	
		40120	P592		750	
		40160	P592		1,000	
		8080	P591		500	
		80160	P592		1,000	
		808040	P594		—	
		8080	P591		500	
		4040	P588		250	
		4080	P590		250	
3面溝 1面フラット	HFPFB NFFSFB	4040	P588	260	250	
		4080	P591		500	
2面溝 2面フラット	HFSTB NFFSTB	4040	P588	260	250	
		4080	P591		500	
対面2面溝	HFSHB EFSHB	4040	P588	260	250	
		4080	P590		500	
1面溝3面フラット	HFSCB EFSCB	4040	P588	260	250	
		4080	P589		500	
ライトタイプ	HFSLB HFS30AB	4040	P587	212	250	
		4080	P593		500	
角度付	HFS45AB HFS60AB	40	P593	213	—	
		—	P593		—	
黒アルマイト	HFSBB EFSBB NFFSBB EFSBB	4040	P593	219	250	
		4080	P589		500	
		8080	P591		1,000	
		80160	P592		250	
		4040	P588		—	
		4080	P588		—	
		4040	P587		250	
		4080	P589		500	
		4040	P589		500	
		4080	P589		500	
曲面	HFSRB NFSRB	4040	P594	260	—	
		803040	P594		—	
4面溝	HFSB GFSB EFSB NFSB NFSB CAFB	4545	P625	260	250	
		45180	P629		500	
		4590	P628		1,000	
		50100	P632		250	
		5050	P631		500	
		6050	P633		500	
		9090	P629		1,000	
		90180	P629		—	
		909045	P630		—	
		100100	P632		500	
3面溝 1面フラット	HFPFB GFSFB	4545	P626	260	250	
		4590	P628		—	
2面溝 2面フラット	HFSTB EFSFB	4545	P627	260	250	
		5050	P631		—	
対面2面溝	HFSHB EFSHB	4545	P627	260	250	
		5050	P631		—	
1面溝3面フラット	HFSCB EFSCB	4545	P627	260	250	
		5050	P631		—	
ライトタイプ 4面溝 3面溝 2面溝	HFSLB NFSLB	4545	P625	212	250	
		4590	P628		500	
角度付	HFS45AB HFS60AB	45	P630	213	—	
		—	P630		—	
黒アルマイト	HFSBB EFSBB NFFSBB EFSBB	4545	P625	260	250	
		4590	P628		500	
		45180	P629		1,000	
		5050	P631		250	
		50100	P632		500	
		9090	P629		—	
		90180	P629		1,000	
		4545	P625		250	
		4545	P627		250	
		曲面	HFSRB NFSRB		4545	P630
909045	P630			—		