

表組の数値を訂正。

型式	D	B 選択	D ₁	d ₁	C	止めネジ M×長さ	¥基準単価						
							SCCN	PSCCN	SSCCN	SCCA	SCCAW	SCCAB	
(スタンダードタイプ) SCCN PSCCN SSCCN SCCA SCCAW SCCAB	3	+0.05 +0.01	*6 8	7	4.5	0.2	M3×3	60	150	160	110	180	210
	4		*6 8	8	5.5			80	160	160	120	190	220
	5		*6 8 10	11	10		75	180	190	130	220	250	
	6		*6 *8 *10	12	11		85	180	190	140	220	250	
	8		*6 *8 *10	14	12		90	230	220	150	230	260	
	10		*6 *8 *10	16	13		90	230	220	180	240	270	
	12		6 *8 *10 12	20	15	0.5	M5×4 B6のみ M4×3	100	270	260	190	250	280
	13		*8 10 12	22	18			150	280	270	200	—	—
	15		*8 *10 *12	24	20		170	320	300	220	300	350	
	16		8 *10 12 15	26	22		180	350	310	230	340	—	
	18・20		*10 *12 *15	32	27		170	380	380	260	420	450	
	25		*12 15 18	38	31		220	490	620	380	480	—	
	30		*15 18 20	46	38	1	M8×6	310	630	680	390	660	710
	35		*15 18 20	50	40			390	810	1,000	600	—	—
	40		*20 22	60	45		M10×8	660	950	1,400	850	990	—
	50		20 *22 25	70	55			750	1,140	1,680	990	1,270	1,320

<訂正用>

+0.05 +0.01
