

表組の数値を訂正。

<訂正用>

H	寸 L	Y基準単価				C-SHWT	C-SH2R
		1ブロック		2ブロック			
		C-SHR	C-SHWT	C-SH2R	C-SH2WT		
24 (SHWT) 28 (SHR)	220	3,590	3,690	5,590	5,790	3,690	5,590
	280	3,920	4,050	5,940	6,120	4,050	5,940
	340	4,260	4,390	6,270	6,460	4,390	6,270
	400	4,590	4,740	6,600	6,810	4,740	6,600
	460	4,940	5,080	6,940	7,160	5,080	6,940
	520	5,270	5,430	7,280	7,500	5,430	7,280
	580	5,600	5,780	7,620	7,850	5,780	7,620
	640	5,940	6,120	7,950	8,190	6,120	7,950
	700	6,280	6,470	8,280	8,540	6,470	8,280
	760	6,620	6,820	8,620	8,890	6,820	8,620
	820	6,950	7,160	8,960	9,240	7,160	8,960
	880	7,290	7,510	9,290	9,580	7,510	9,290
	940	7,630	7,860	9,630	9,930	7,860	9,630
	1000	7,960	8,200	9,970	10,280	8,200	9,970
	1060	8,290	8,550	10,310	10,620	8,550	10,310
	1120	8,640	8,900	10,640	10,970	8,900	10,640
	1180	8,970	9,250	10,980	11,320	9,250	10,980
	1240	9,310	9,590	11,320	11,670	9,590	11,320
	1300	9,640	9,940	11,650	12,010	9,940	11,650
	1360	9,980	10,290	11,990	12,360	10,290	11,990
1420	10,320	10,630	12,330	12,700	10,630	12,660	
1480	10,650	10,980	12,660	13,050	10,980	12,990	
1540	10,990	11,330	13,000	13,400	11,330	13,330	
1600	11,330	11,670	13,330	13,750	11,670	13,670	
1660	11,660	12,020	13,670	14,090	12,020	14,010	
1720	12,000	12,370	14,010	14,440	12,370	14,340	
1780	12,330	12,710	14,340	14,790	12,710	14,680	
1840	12,670	13,060	14,680	15,130	13,060	15,020	
1900	13,010	13,410	15,020	15,480	13,410	15,350	
1960	13,340	13,760	15,350	15,830	13,760	15,690	
220	3,980	4,100	6,210	6,400	4,100	6,210	
280	4,350	4,490	6,590	6,790	4,490	6,590	
340	4,720	4,870	6,960	7,170	4,870	6,960	
400	5,100	5,260	7,330	7,550	5,260	7,330	
460	5,480	5,640	7,710	7,950	5,640	7,710	
520	5,850	6,030	8,080	8,330	6,030	8,080	
580	6,220	6,420	8,460	8,720	6,420	8,460	
640	6,600	6,800	8,830	9,100	6,800	8,830	
700	6,970	7,180	9,200	9,480	7,180	9,200	
760	7,350	7,570	9,580	9,870	7,570	9,580	
820	7,720	7,950	9,950	10,260	7,950	9,950	
880	8,090	8,340	10,320	10,640	8,340	10,320	
940	8,470	8,730	10,700	11,050	8,730	10,700	
1000	8,840	9,110	11,070	11,420	9,110	11,070	
1060	9,210	9,500	11,450	11,830	9,500	11,450	
1120	9,590	9,890	11,820	12,180	9,890	11,820	
1180	9,960	10,270	12,190	12,570	10,270	12,190	
1240	10,340	10,650	12,570	12,960	10,650	12,960	
1300	10,710	11,040	12,940	13,340	11,040	13,320	
1360	11,080	11,430	13,320	13,730	11,430	13,690	
1420	11,460	11,810	13,690	14,110	11,810	14,060	
1480	11,830	12,190	14,060	14,490	12,190	14,440	
1540	12,210	12,580	14,440	14,880	12,580	14,440	
1600	12,580	12,960	14,810	15,270	12,960	14,810	
1660	12,950	13,350	15,180	15,650	13,350	15,180	
1720	13,330	13,740	15,560	16,040	13,740	15,560	
1780	13,700	14,120	15,930	16,410	14,120	15,930	
1840	14,070	14,510	16,310	16,810	14,510	16,680	
1900	14,450	14,890	16,680	17,190	14,890	17,050	
1960	14,820	15,280	17,050	17,580	15,280	17,480	
220	4,620	4,770	7,480	7,710	4,770	7,480	
280	5,010	5,160	7,860	8,100	5,160	7,860	
340	5,380	5,550	8,240	8,490	5,550	8,240	
400	5,760	5,940	8,610	8,880	5,940	8,610	
460	6,140	6,330	9,000	9,270	6,330	9,000	
520	6,520	6,720	9,370	9,660	6,720	9,370	
580	6,900	7,110	9,750	10,050	7,110	9,750	
640	7,280	7,510	10,130	10,440	7,510	10,130	
700	7,660	7,890	10,510	10,840	7,890	10,510	
760	8,040	8,290	10,890	11,230	8,290	10,890	
820	8,420	8,680	11,270	11,620	8,680	11,270	
880	8,800	9,070	11,650	12,010	9,070	11,650	
940	9,180	9,460	12,030	12,400	9,460	12,030	
1000	9,560	9,850	12,410	12,790	9,850	12,410	
1060	9,940	10,240	12,790	13,180	10,240	12,790	
1120	10,320	10,640	13,170	13,570	10,640	13,170	
1180	10,700	11,030	13,550	13,970	11,030	13,550	
1240	11,070	11,420	13,930	14,360	11,420	13,930	
1300	11,460	11,810	14,310	14,750	11,810	14,310	
1360	11,830	12,200	14,690	15,140	12,200	14,690	
1420	12,210	12,590	15,070	15,530	12,590	15,070	
1480	12,590	12,980	15,450	15,920	12,980	15,450	
1540	12,970	13,370	15,830	16,320	13,370	15,830	
1600	13,350	13,760	16,200	16,710	13,760	16,200	
1660	13,730	14,160	16,590	17,100	14,160	16,590	
1720	14,110	14,550	16,960	17,490	14,550	16,960	
1780	14,490	14,940	17,340	17,880	14,940	17,340	
1840	14,870	15,330	17,720	18,270	15,330	17,720	
1900	15,250	15,720	18,100	18,660	15,720	18,100	
1960	15,630	16,110	18,480	19,050	16,110	18,480	
280	5,720	5,890	9,110	9,390	5,890	9,110	
360	6,240	6,430	9,630	9,920	6,430	9,630	
440	6,750	6,960	10,140	10,450	6,960	10,140	
520	7,270	7,490	10,660	10,980	7,490	10,660	
600	7,790	8,030	11,180	11,520	8,030	11,180	
680	8,300	8,560	11,690	12,050	8,560	11,690	
760	8,820	9,090	12,210	12,580	9,090	12,210	
840	9,330	9,620	12,720	13,120	9,620	12,720	
920	9,850	10,160	13,240	13,650	10,160	13,240	
1000	10,370	10,690	13,760	14,180	10,690	13,760	
1080	10,890	11,220	14,280	14,720	11,220	14,280	
1160	11,400	11,760	14,790	15,250	11,760	14,790	
1240	11,920	12,290	15,310	15,780	12,290	15,310	
1320	12,440	12,820	15,830	16,320	12,820	15,830	
1400	12,950	13,350	16,340	16,850	13,350	16,340	
1480	13,470	13,890	16,860	17,380	13,890	16,860	
1560	13,990	14,420	17,380	17,910	14,420	17,380	
1640	14,500	14,950	17,890	18,450	14,950	17,890	
1720	15,020	15,480	18,410	18,980	15,480	18,410	
1800	15,540	16,020	18,930	19,510	16,020	18,930	
1880	16,050	16,550	19,440	20,040	16,550	19,440	
1960	16,570	17,080	19,960	20,580	17,080	19,960	

C-SHWT	C-SH2R
3,690	5,590
4,050	5,940
4,390	6,270
4,740	6,600
5,080	6,940
5,430	7,280
5,780	7,620
6,120	7,950
6,470	8,280
6,820	8,630
7,160	8,960
7,510	9,290
7,860	9,630
8,200	9,970
8,550	10,310
8,900	10,640
9,250	10,980
9,590	11,320
9,940	11,650
10,290	11,990
10,630	12,330
10,980	12,660
11,330	13,000
11,670	13,330
12,020	13,670
12,370	14,010
12,710	14,340
13,060	14,680
13,410	15,020
13,760	15,350
4,100	6,210
4,490	6,590
4,870	6,960
5,260	7,330
5,640	7,710
6,030	8,080
6,420	8,460
6,800	8,830
7,180	9,200
7,570	9,580
7,950	9,950
8,340	10,320
8,730	10,700
9,110	11,070
9,500	11,450
9,890	11,830
10,270	12,180
10,650	12,570
11,040	12,960
11,430	13,340
11,810	13,690
12,190	14,060
12,580	14,440
12,960	14,810
13,350	15,180
13,740	15,560
14,120	15,930
14,510	16,310
14,890	16,680
15,280	17,050
4,770	7,480
5,160	7,860
5,550	8,240
5,940	8,610
6,330	9,000
6,720	9,370
7,110	9,750
7,510	10,130
7,890	10,510
8,290	10,890
8,680	11,270
9,070	11,650
9,460	12,030
9,850	12,410
10,240	12,790
10,640	13,170
11,030	13,550
11,420	13,930
11,810	14,310
12,200	14,690
12,590	15,070
12,980	15,450
13,370	15,830
13,760	16,200
14,160	16,590
14,550	16,960
14,940	17,340
15,330	17,720
15,720	18,100
16,110	18,480
5,890	9,110
6,430	9,630
6,960	10,140
7,490	10,660
8,030	11,180
8,560	11,690
9,090	12,210
9,620	12,720
10,160	13,240
10,690	13,760
11,220	14,280
11,760	14,790
12,290	15,310
12,820	15,830
13,350	16,340
13,890	16,850
14,420	17,380
14,950	17,890
15,480	18,410
16,020	18,930
16,550	19,440
17,080	19,960

表組の数値を訂正。

<訂正用>

寸寸 L	▼基準単位			
	1ブロック		2ブロック	
	C-SER	C-SEWT	C-SE2R	C-SE2WT
220	4,370	4,510	6,990	7,210
280	4,740	4,890	7,370	7,590
340	5,120	5,280	7,740	7,980
400	5,490	5,660	8,120	8,370
460	5,870	6,050	8,490	8,750
520	6,240	6,430	8,860	9,140
580	6,610	6,820	9,240	9,520
640	6,990	7,200	9,610	9,910
700	7,360	7,590	9,990	10,290
760	7,740	7,970	10,360	10,680
820	8,110	8,360	10,730	11,060
880	8,480	8,740	11,110	11,450
940	8,860	9,130	11,480	11,840
1000	9,230	9,520	11,850	12,220
1060	9,600	9,900	12,230	12,610
1120	9,980	10,290	12,600	12,990
1180	10,350	10,670	12,980	13,380
1240	10,730	11,060	13,350	13,760
1300	11,100	11,440	13,720	14,150
1360	11,470	11,830	14,100	14,530
1420	11,850	12,210	14,470	14,920
1480	12,220	12,600	14,850	15,300
1540	12,600	12,980	15,220	15,690
1600	12,970	13,370	15,590	16,070
1660	13,340	13,750	15,970	16,460
1720	13,720	14,140	16,340	16,850
1780	14,090	14,530	16,710	17,230
1840	14,460	14,910	17,090	17,620
1900	14,840	15,300	17,460	18,000
1960	15,210	15,680	17,840	18,390
220	5,100	5,250	8,420	8,680
280	5,480	5,640	8,800	9,070
340	5,860	6,040	9,180	9,460
400	6,240	6,430	9,560	9,850
460	6,620	6,820	9,940	10,250
520	6,990	7,210	10,320	10,640
580	7,380	7,600	10,700	11,030
640	7,750	7,990	11,080	11,420
700	8,130	8,380	11,460	11,810
760	8,510	8,770	11,840	12,200
820	8,890	9,170	12,220	12,590
880	9,270	9,560	12,600	12,980
940	9,650	9,950	12,980	13,380
1000	10,030	10,340	13,350	13,770
1060	10,410	10,730	13,740	14,160
1120	10,790	11,120	14,110	14,550
1180	11,170	11,520	14,490	14,940
1240	11,550	11,910	14,870	15,330
1300	11,930	12,300	15,250	15,720
1360	12,310	12,690	15,630	16,110
1420	12,690	13,080	16,010	16,510
1480	13,070	13,470	16,390	16,890
1540	13,440	13,860	16,770	17,290
1600	13,830	14,250	17,150	17,680
1660	14,200	14,640	17,530	18,070
1720	14,580	15,030	17,910	18,460
1780	14,960	15,420	18,290	18,850
1840	15,340	15,820	18,670	19,240
1900	15,720	16,210	19,050	19,640
1960	16,100	16,600	19,430	20,030
280	6,260	6,450	10,180	10,500
360	6,770	6,980	10,700	11,030
440	7,290	7,510	11,220	11,560
520	7,810	8,050	11,730	12,090
600	8,320	8,580	12,250	12,630
680	8,840	9,110	12,770	13,160
760	9,360	9,640	13,290	13,690
840	9,870	10,180	13,800	14,230
920	10,390	10,710	14,320	14,760
1000	10,910	11,240	14,830	15,290
1080	11,430	11,780	15,350	15,830
1160	11,940	12,310	15,870	16,360
1240	12,460	12,840	16,380	16,890
1320	12,970	13,370	16,900	17,420
1400	13,490	13,910	17,420	17,960
1480	14,010	14,440	17,940	18,490
1560	14,520	14,970	18,450	19,020
1640	15,040	15,510	18,970	19,560
1720	15,560	16,040	19,490	20,090
1800	16,080	16,560	20,000	20,620
1880	16,590	17,100	20,520	21,150
1960	17,110	17,640	21,040	21,690

30

36 (C-SEWT)
40 (C-SER)

42 (C-SEWT)
45 (C-SER)

C-SEWT	C-SE2R
4,510	6,990
4,890	7,370
5,280	7,740
5,660	8,120
6,050	8,490
6,430	8,860
6,820	9,240
7,200	9,610
7,590	9,990
7,970	10,360
8,360	10,730
8,740	11,110
9,130	11,480
9,520	11,850
9,900	12,230
10,290	12,600
10,670	12,980
11,060	13,350
11,440	13,720
11,830	14,100
12,210	14,470
12,600	14,850
12,980	15,220
13,370	15,590
13,750	15,970
14,140	16,340
14,530	16,710
14,910	17,090
15,300	17,460
15,680	17,840
5,250	8,420
5,640	8,800
6,040	9,180
6,430	9,560
6,820	9,940
7,210	10,320
7,600	10,700
7,990	11,080
8,380	11,460
8,770	11,840
9,170	12,220
9,560	12,600
9,950	12,980
10,340	13,350
10,730	13,740
11,120	14,110
11,520	14,490
11,910	14,870
12,300	15,250
12,690	15,630
13,080	16,010
13,470	16,390
13,860	16,770
14,250	17,150
14,640	17,530
15,030	17,910
15,420	18,290
15,820	18,670
16,210	19,050
16,600	19,430
6,450	10,180
6,980	10,700
7,510	11,220
8,050	11,730
8,580	12,250
9,110	12,770
9,640	13,290
10,180	13,800
10,710	14,320
11,240	14,830
11,780	15,350
12,310	15,870
12,840	16,380
13,370	16,890
13,910	17,420
14,440	17,940
14,970	18,450
15,510	18,970
16,040	19,490
16,560	20,000
17,100	20,520
17,640	21,040