

赤枠内 L寸法指定範囲を修正

## ■軸径(D)固定タイプ

H	型式		L	DC	N	SV	
	Type	D	指定0.01mm単位	指定0.005mm単位	指定0.1mm単位	指定0.5mm単位	
2	GV-CPV-L	0.5	15.00~60.00				
3	GV-CPZ-L GV-CPV-L	0.6	15.00~100.00	$(D-0.08) \leq DC \leq D$ DC=Dの場合 DCXと指定	0.3~10.0	2.0~50.0	
		0.7					
		0.8					
		0.9					
		1					
		1.2					
		1.5					
4		2					
5		2.5					
6		3					
7		3.5	15.00~120.00				
		4					
8		4.5					
9		5					
10		6					
11		7					
15		8					
18		10					
		13					