

規格表赤枠部 B寸10、L寸16は規格廃止
 価格表赤枠部 基準単価の対象となる本数は1~3本

型式		L			H許容差	C	L	公差
Type	B _{H9}							
KED KEDS (ステンレス)	2 ⁰ _{-0.025}	10	15	20	2 ⁰ _{-0.025}	0.16~0.25	10	⁰ _{-0.15}
	3	10	15	20 25 30	3 ⁰ _{-0.025}		12 15 16 18	⁰ _{-0.18}
	4	10	12	15 16 18 20 25 30 35 40 45 50	4 ⁰ _{-0.030}		20 25 30	⁰ _{-0.21}
	5	10	12	15 16 18 20 25 30 35 40 45 50	5 ⁰ _{-0.030}		35 40 45 50	⁰ _{-0.25}
	6	10	12	15 16 18 20 25 30 35 40 45 50 55 60	6 ⁰ _{-0.036}		55 60 70 80	⁰ _{-0.30}
	7	15	20	25 30 35 40 45 50 55 60	7 ⁰ _{-0.036}		90 100 110	⁰ _{-0.35}
KES KESS (ステンレス)	8 ⁰ _{-0.036}	15	16	18 20 25 30 35 40 45 50 55 60 70 80	8 ⁰ _{-0.090}	0.25~0.40		
	10	15	18	20 25 30 35 40 45 50 55 60 70 80				
	12	20	25	30 35 40 45 50 55 60 70 80				
KEG KEGS (ステンレス)	14 ⁰ _{-0.043}	30 35 40 45 50 55 60 70 80 90			9 ⁰ _{-0.110}	0.40~0.60		
	15	30 35 40 45 50 55 60 70 80 90						
	16	40 45 50 55 60 70 80 90 100						
	18	40 45 50 55 60 70 80 90 100 110						



Order
注文例

型式 - L
KED6 - 30



Price
価格



Delivery
出荷日

B2~12
在庫品 翌日出荷 P.47
 ご希望によりPM5:00迄、当日出荷受付致します。

B14~18
3 日目発送

ストックT 400円/1本
 ストックA 200円/1本 P.48
 同一サイズ3本以上は一律540円(ストックTは除く)



Alterations
追加加工

型式 - L(C)
KED6 - LC28

3 日目発送
 ストックT 400円/1本
 ストックA 200円/1本 P.48
 同一サイズ3本以上は一律540円(ストックTは除く)

B	KED KES KEG			KEDS KESS KEGS		
	¥基準単価	¥スライド単価		¥基準単価	¥スライド単価	
	1~3本	4~19	20~100	1~3本	4~19	20~100
2	220	170	80	280	210	160
3	220	170	80	280	210	150
4	220	170	80	280	210	150
5	240	170	90	290	220	170
6	240	170	90	290	230	170
7	260	180	105	320	240	180
8	260	180	110	320	260	180
10	290	180	110	370	290	220
12	300	180	130	400	310	240
14	360	280	235	600	500	440
15	390	310	260	670	550	500
16	440	360	305	750	600	550
18	500	410	340	850	680	620

表示数量超えは価格・出荷日お見積り

Alteration	Code	Spec.	¥/1Code																													
全長変更 	LC	L寸法を1mm単位で指定できます。	200																													
		<table border="1"> <thead> <tr> <th>B</th> <th>LC範囲</th> <th>B</th> <th>LC範囲</th> </tr> </thead> <tbody> <tr> <td>2</td> <td>5~20</td> <td>10</td> <td>15~80</td> </tr> <tr> <td>3</td> <td>6~30</td> <td>12</td> <td>20~80</td> </tr> <tr> <td>4</td> <td>8~50</td> <td>14</td> <td>25~90</td> </tr> <tr> <td>5</td> <td>8~50</td> <td>15</td> <td>25~90</td> </tr> <tr> <td>6</td> <td>10~60</td> <td>16</td> <td>35~100</td> </tr> <tr> <td>7</td> <td>15~60</td> <td>18</td> <td>35~110</td> </tr> <tr> <td>8</td> <td>15~80</td> <td></td> <td></td> </tr> </tbody> </table>		B	LC範囲	B	LC範囲	2	5~20	10	15~80	3	6~30	12	20~80	4	8~50	14	25~90	5	8~50	15	25~90	6	10~60	16	35~100	7	15~60	18	35~110	8
B	LC範囲	B	LC範囲																													
2	5~20	10	15~80																													
3	6~30	12	20~80																													
4	8~50	14	25~90																													
5	8~50	15	25~90																													
6	10~60	16	35~100																													
7	15~60	18	35~110																													
8	15~80																															