

シャフト めねじ2穴タイプ ストレートタイプの表記を修正

■ストレートタイプ

Catalog No.		¥単価											
Type	D	最短L 50	L51 100	L101 150	L151 200	L201 300	L301 400	L401 500	L501 600	L601 800	L801 1000	L1001 1200	L1201 1500
SFDJ	15	1,820	1,950	2,080	2,210	2,540	2,860	3,180	3,490	4,860	—	—	—
	16	1,820	1,950	2,080	2,210	2,540	2,860	3,180	3,490	4,860	—	—	—
	18	1,820	1,950	2,080	2,210	2,540	2,860	3,180	3,490	4,860	5,500	—	—
	20	1,820	1,950	2,080	2,210	2,540	2,860	3,180	3,490	4,860	5,500	—	—
	25	2,270	2,430	2,610	2,760	3,170	3,590	4,000	4,400	5,930	6,750	7,570	—
	30	2,710	2,910	3,100	3,270	3,740	4,200	4,660	5,130	6,770	7,720	9,560	11,360
	35	3,050	3,290	3,480	3,710	4,260	4,670	5,210	5,740	7,470	8,520	9,590	11,350
	40	3,510	3,790	4,060	4,320	4,980	5,500	6,150	6,790	8,760	10,080	11,320	13,420
	50	4,440	4,440	4,780	5,150	6,020	6,700	7,560	8,330	10,810	12,550	14,210	16,940
	15	2,480	2,840	3,230	3,600	4,280	4,950	5,460	5,980	8,190	—	—	—
SSFJD	16	2,480	2,840	3,230	3,600	4,280	4,950	5,460	5,980	8,190	—	—	—
	18	2,480	2,840	3,230	3,600	4,280	4,950	5,460	5,980	8,190	9,420	—	—
	20	2,480	2,840	3,230	3,600	4,280	4,950	5,460	5,980	8,190	9,420	—	—
	25	2,980	3,430	3,850	4,270	5,110	5,950	6,580	7,180	9,240	11,160	13,520	—
	30	3,520	4,030	4,520	5,000	5,960	6,910	7,590	8,250	10,650	12,840	15,570	18,820
	35	3,910	4,470	5,000	5,520	6,580	7,440	8,630	9,810	12,470	14,840	17,210	20,820
	40	4,770	5,580	6,330	7,090	8,140	8,960	10,420	11,890	15,170	18,100	21,030	25,480
	50	6,750	6,750	7,770	8,770	10,390	11,690	13,370	15,770	20,570	24,780	28,950	35,310
	15	2,970	3,250	3,670	3,940	4,850	5,610	6,370	—	—	—	—	—
	RSFDJ	16	2,970	3,250	3,670	3,940	4,850	5,610	6,370	—	—	—	—
18		2,970	3,540	4,100	4,520	5,570	6,610	7,000	—	—	—	—	—
20		2,970	3,540	4,100	4,520	5,570	6,610	7,000	—	—	—	—	—
25		3,700	4,450	5,200	5,930	6,860	8,260	9,530	—	—	—	—	—
30		4,430	5,360	6,400	6,830	8,640	9,820	11,470	—	—	—	—	—
PSFDJ	15	1,920	2,090	2,270	2,450	2,890	3,330	3,790	4,240	6,120	—	—	—
	16	1,920	2,090	2,270	2,450	2,890	3,330	3,790	4,240	6,120	—	—	—
	18	1,920	2,090	2,270	2,450	2,890	3,330	3,790	4,240	6,120	6,990	—	—
	20	1,920	2,090	2,270	2,450	2,890	3,330	3,790	4,240	6,120	6,990	—	—
	25	2,380	2,640	2,850	3,070	3,640	4,200	4,750	5,310	7,420	8,550	9,690	—
	30	2,830	3,110	3,360	3,620	4,260	4,900	5,540	6,170	8,430	9,720	12,270	14,750
	35	3,180	3,480	3,760	4,040	4,750	5,300	6,000	6,700	8,960	10,350	12,360	14,820
	40	3,670	4,040	4,380	4,730	5,590	6,290	7,120	7,960	10,520	12,250	13,870	16,610
	50	4,750	4,750	5,210	5,660	6,810	7,750	8,870	10,000	13,090	15,360	17,530	21,090
	PSSFDJ	15	2,830	3,380	3,930	4,490	5,470	6,470	7,220	7,970	11,220	—	—
16		2,830	3,380	3,930	4,490	5,470	6,470	7,220	7,970	11,220	—	—	—
18		2,830	3,380	3,930	4,490	5,470	6,470	7,220	7,970	11,220	13,030	—	—
20		2,830	3,380	3,930	4,490	5,470	6,470	7,220	7,970	11,220	13,030	—	—
25		3,360	4,000	4,630	5,250	6,490	7,720	8,630	9,540	12,550	15,370	18,840	—
30		3,960	4,700	5,430	6,120	7,530	8,930	9,910	10,900	14,420	17,610	21,620	26,520
35		4,340	5,120	5,870	6,600	8,120	9,380	11,060	12,740	16,510	19,860	23,210	28,320
40		5,380	6,500	7,580	8,640	10,160	11,350	13,440	15,510	20,170	24,320	28,470	34,780
50		8,020	8,020	9,450	10,890	13,180	15,070	17,950	20,840	27,640	33,600	39,540	48,530

<訂正用>

RSFDJ