

肉厚スタンダードタイプ

Catalog No.		H 選択						L	H ₁	T	S	W	止めネジ M	L ₁	d	¥単価 1~4コ		
Type	D	10	20	25	30	40	SHTBN									SHTMN	SHTSN	
SHTBN SHTMN SHTSN	10	20	25	30	40		42	H+10	15	6	18	M6	30	6.6	2,280	2,330	3,710	
	12	20	25	30	40			H+11	18						2,400	2,450	4,400	
	13	20	25	30	40			H+12							2,600	2,650	4,540	
	15	25	30	40			54	H+15	20	30	M6	42	6.6	3,190	3,240	4,940		
	16	25	30	40				H+15						3,390	3,440	5,080		
	20	25	30	40	50	60	67	H+18	25	8	35	M8	50	9	4,100	4,150	7,600	
	25	30	40	50	60			H+20	30						4,650	4,700	8,190	
	30	30	40	50	60		85	H+23	35	10	45	M8	65	6.6	5,980	6,030	9,990	
	35	30	50	60				H+25							7,130	7,230	10,320	
	40	40	60	80			100	H+30	40		60		80	9	7,830	7,930	12,300	
50	40	60	80			125	H+38	50	15	75		100	11	9,480	9,620	14,450		

肉厚スリットタイプ

Catalog No.		H 選択						L	H ₁	T	S	W	L ₁	d	E	締付ボルト M	d ₂	d ₁	ℓ	C	¥単価 1~4コ		
Type	D	10	20	25	30	40	SHSTBN														SHSTMN	SHSTSN	
SHSTBN SHSTMN SHSTSN	10	20	25	30	40		48	H+19	15	6	24	36	6.6	14	M6貫通	6.6	11	6.5	2	2,520	2,520	5,370	
	12	20	25	30	40			H+21	18											2,640	2,640	6,250	
	13	20	25	30	40			H+23	20											2,880	2,890	6,450	
	15	25	30	40			54	H+23	20	30	42	16	M6貫通	9	14	9	3	3,590	3,630	7,060			
	16	25	30	40				H+29	25									3,830	3,880	7,260			
	20	25	30	40	50	60	67	H+29	25	8	35	50	9	19	M8貫通	9	14	9	4,820	4,870	10,210		
	25	30	40	50	60			H+31	30										4,990	5,040	10,740		
	30	30	40	50	60		85	H+33	35	10	45	65	6.6	24	M8貫通	9	14	9	3	6,400	6,450	11,940	
	35	30	50	60				H+36												7,220	7,320	12,800	
	40	40	60	80			100	H+38	40		60	80	9	29	M8深16					8,370	8,470	15,560	
50	40	60	80			125	H+51	50	15	75	100	11	38	M12深24	14	20	13		10,760	10,980	17,790		

<訂正用>

1

L
42
54
67
85
100
125

2

L
48
54
67
85
100
125