

中荷重用スライドガイド SVRB価格を一部修正

<訂正用>

6,030

Catalog No. Type	定寸 H	取付 穴数 L	¥単価 1~4コ				ルール						
			SVRZ	SVWZ	SVWTZ	SV2RZ	SV2WZ	SV2WTZ	SRZL	SVRB	SVWB	SVWTB	
(セット品) -ブロック1コー SVRZ SVWZ SVWTZ	24	160	3	9,030	9,670	9,800	14,250	15,520	15,800	4,020			
		220	4	9,640	10,270	10,400	14,860	16,130	16,400	4,660			
		280	5	10,200	10,820	10,950	15,410	16,680	16,950	5,250			
		340	6	10,860	11,490	11,620	16,080	17,340	17,620	5,950			
		400	7	11,710	12,350	12,470	16,930	18,200	18,470	6,850			
		460	8	12,570	13,200	13,330	17,790	19,060	19,330	7,760			
		520	9	13,430	14,050	14,180	18,640	19,910	20,180	8,660			
		580	10	14,280	14,910	15,040	19,500	20,770	21,040	9,570			
		640	11	15,130	15,770	15,900	20,350	21,620	21,890	10,470			
		700	12	15,990	16,630	16,750	21,210	22,480	22,750	11,380			
		760	13	16,850	17,480	17,610	22,060	23,330	23,600	12,280			
		820	14	17,700	18,340	18,460	22,920	24,190	24,460	13,190	5,530	6,200	6,350
		880	15	18,560	19,200	19,320	23,780	25,050	25,320	14,090			
		940	16	19,420	20,050	20,170	24,630	25,900	26,170	15,000			
		1000	17	20,270	20,910	21,030	25,490	26,760	27,030	15,900			
		1060	18	21,130	21,760	21,880	26,340	27,610	27,880	16,810			
		1120	19	21,980	22,610	22,740	27,200	28,470	28,740	17,710			
		1180	20	22,840	23,470	23,600	28,050	29,320	29,600	18,620			
		1240	21	23,690	24,330	24,450	28,910	30,180	30,450	19,520			
		1300	22	24,550	25,190	25,310	29,770	31,030	31,310	20,420			
1360	23	25,410	26,040	26,160	30,620	31,890	32,160	21,330					
1420	24	26,260	26,900	27,020	31,480	32,740	33,020	22,230					
1480	25	27,120	27,760	27,870	32,330	33,600	33,870	23,140					
-ブロック2コー SV2RZ SV2WZ SV2WTZ	28	220	4	10,080	11,080	11,580	15,500	17,510	18,530	4,890			
		280	5	10,870	11,870	12,370	16,290	18,300	19,320	5,730			
		340	6	11,860	12,860	13,360	17,290	19,300	20,320	6,780			
		400	7	12,860	13,860	14,360	18,280	20,290	21,310	7,830			
		460	8	13,850	14,850	15,350	19,280	21,290	22,310	8,890			
		520	9	14,840	15,840	16,350	20,270	22,280	23,300	9,940			
		580	10	15,840	16,840	17,340	21,270	23,280	24,300	10,990			
		640	11	16,830	17,840	18,340	22,260	24,270	25,290	12,050			
		700	12	17,830	18,840	19,330	23,260	25,270	26,290	13,090			
		760	13	18,820	19,830	20,330	24,250	26,260	27,280	14,150			
		820	14	19,830	20,830	21,320	25,250	27,260	28,280	15,200			
		880	15	20,820	21,820	22,320	26,240	28,250	29,270	16,260			
		940	16	21,810	22,820	23,310	27,240	29,250	30,270	17,310			
		1000	17	22,810	23,810	24,310	28,230	30,240	31,260	18,360			
		1060	18	23,800	24,810	25,300	29,230	31,240	32,260	19,410			
		1120	19	24,800	25,800	26,300	30,220	32,230	33,250	20,460	5,750	6,810	7,360
		1180	20	25,790	26,800	27,300	31,220	33,230	34,250	21,520			
		1240	21	26,800	27,800	28,290	32,210	34,220	35,240	22,570			
		1300	22	27,790	28,790	29,290	33,210	35,220	36,240	23,630			
		1360	23	28,780	29,790	30,280	34,200	36,210	37,230	24,670			
1420	24	29,780	30,780	31,280	35,200	37,210	38,230	25,720					
1480	25	30,770	31,780	32,270	36,200	38,200	39,220	26,780					
1540	26	31,770	32,770	33,270	37,190	39,200	40,220	27,830					
1600	27	32,760	33,770	34,260	38,190	40,190	41,210	28,890					
1660	28	33,760	34,760	35,260	39,180	41,190	42,210	29,930					
1720	29	34,750	35,760	36,250	40,180	42,180	43,200	30,990					
1780	30	35,750	36,760	37,250	41,170	43,180	44,200	32,040					
1840	31	36,750	37,750	38,240	42,170	44,170	45,200	33,090					
1900	32	37,740	38,750	39,240	43,160	45,170	46,190	34,150					
1960	33	38,740	39,740	40,230	44,160	46,160	47,190	35,190					
-ブロック3コー SV3RZ SV3WZ SV3WTZ	33	220	4	11,220	12,430	12,780	16,910	19,340	20,050	5,830			
		280	5	11,940	13,150	13,500	17,630	20,060	20,770	6,580			
		340	6	12,600	13,810	14,160	18,290	20,720	21,430	7,280			
		400	7	13,680	14,900	15,230	19,370	21,800	22,510	8,430			
		460	8	14,760	15,980	16,310	20,450	22,880	23,590	9,570			
		520	9	15,830	17,050	17,390	21,530	23,960	24,670	10,710			
		580	10	16,910	18,130	18,470	22,610	25,040	25,740	11,840			
		640	11	17,990	19,210	19,550	23,680	26,110	26,820	12,990			
		700	12	19,070	20,280	20,630	24,760	27,190	27,900	14,130			
		760	13	20,150	21,360	21,710	25,840	28,270	28,980	15,270			
		820	14	21,230	22,440	22,790	26,920	29,350	30,060	16,410			
		880	15	22,310	23,520	23,870	28,000	30,430	31,140	17,560			
		940	16	23,390	24,600	24,940	29,080	31,510	32,220	18,700			
		1000	17	24,470	25,680	26,020	30,160	32,590	33,300	19,830			
		1060	18	25,550	26,760	27,100	31,240	33,670	34,380	20,970			
		1120	19	26,630	27,840	28,180	32,310	34,740	35,450	22,110	6,030	7,310	7,700
		1180	20	27,710	28,920	29,260	33,390	35,820	36,530	23,260			
		1240	21	28,780	30,000	30,340	34,470	36,900	37,610	24,400			
		1300	22	29,860	31,080	31,420	35,550	37,980	38,690	25,540			
		1360	23	30,940	32,160	32,500	36,630	39,060	39,770	26,680			
1420	24	32,020	33,240	33,570	37,710	40,140	40,850	27,820					
1480	25	33,100	34,320	34,650	38,790	41,220	41,930	28,960					
1540	26	34,180	35,400	35,730	39,870	42,300	43,000	30,100					
1600	27	35,260	36,480	36,810	40,950	43,380	44,080	31,240					
1660	28	36,340	37,560	37,890	42,020	44,450	45,160	32,390					
1720	29	37,420	38,640	38,970	43,100	45,530	46,240	33,530					
1780	30	38,500	39,720	40,050	44,180	46,610	47,320	34,670					
1840	31	39,580	40,800	41,130	45,260	47,690	48,400	35,810					
1900	32	40,660	41,870	42,200	46,340	48,770	49,480	36,940					
1960	33	41,740	42,950	43,280	47,420	49,850	50,560	38,090					
(ルール) SRZL	33	280	4	13,070	14,660	15,510	20,080	23,260	24,960	6,420			
		360	5	13,740	15,330	16,180	20,750	23,930	25,630	7,180			
		440	6	15,210	16,800	17,650	22,220	25,400	27,100	8,730			
		520	7	16,680	18,270	19,120	23,690	26,870	28,570	10,290			
		600	8	18,150	19,740	20,590	25,150	28,340	30,040	11,840			
		680	9	19,620	21,210	22,060	26,620	29,810	31,510	13,400			
		760	10	21,090	22,680	23,530	28,090	31,280	32,980	14,950			
		840	11	22,550	24,150	25,000	29,560	32,750	34,450	16,510			
		920	12	24,020	25,620	26,470	31,030	34,220	35,910	18,060			
		1000	13	25,490	27,090	27,930	32,500	35,690	37,380	19,620			
		1080	14	26,960	28,550	29,400	33,970	37,150	38,850	21,180			
		1160	15	28,430	30,020	30,870	35,440	38,620	40,320	22,730			
		1240	16	29,900	31,490	32,340	36,910	40,090	41,790	24,290	7,410	9,100	10,000
		1320	17	31,370	32,960	33,810	38,380	41,560	43,260	25,840			
		1400	18	32,840	34,430	35,280	39,850	43,030	44,730	27,400			
		1480	19	34,310	35,900	36,750	41,310	44,500	46,200	28,950			
		1560	20	35,780	37,370	38,220	42,780	45,970	47,670	30,510			
		1640	21	37,250	38,840	39,690	44,250	47,440	49,140	32,060			
		1720	22	38,710	40,310	41,160	45,720	48,910	50,610	33,620			
		1800	23	40,180	41,780	42,630	47,190	50,380	52,080	35,180			
1880	24	41,650	43,250	44,100	48,660	51,850	53,540	36,730					
1960	25	43,120	44,710	45,560	50,130	53,310	55,010	38,290		</			