

レンチ穴タイプ 赤枠内のL寸法の範囲を一部修正

■レンチ穴タイプ

Catalog No.			D寸公差 g6	P 指定0.01mm単位	L 指定1mm単位	B 指定0.1mm単位	m	(W)	M (並目)	ℓ
Type	形状	D								
FPSW	TA(丸)	8	-0.005 -0.014	6.00~ 8.00	11 (12) ~16	5.0~15.0	3	1.8	M5	8
GFPSW		8T								
BFPSW		10	(8.00)7.00~10.00	11(12)~20	5.0~20.0	2.2		M5	8	
SFPSW	TD(ダイヤ)	12	-0.006 -0.017	(8.00)7.00~12.00	12~24	5.0~20.0	4	2.5	M8	10
HFPSW		13								
CFPSW		16	10.00~16.00	16~32	10.0~20.0	4				
TFPSW		20	13.00~20.00	20~40	10.0~20.0	5		12		

<訂正用>

L 指定1mm単位
11~16
11(12)~20
12~24
13(14)~26
16~32
20~40