

P756 (規格表)

赤枠内 区切り位置を修正

Catalog No.		D寸公差 g6	P 指定0.01mm単位	L 指定1mm単位	B 指定0.1mm単位	(W)	M (並目)	ℓ	
Type	形状								
FPQW GFPQW BFPQW SFPQW HFPQW CFPQW TFPQW	TA (丸)	6	-0.004	6.50~10.00	6(9)~12	5.0~12.0	3.0	M3	5
		6T	-0.012					M2.6	4
		8	-0.005	9.00~13.00	8(12)~16	5.0~15.0	3.5	M5	8
		8T	-0.014					M4	6
	TD (ダイヤ)	10	-0.006 -0.017	11.00~15.00	10(12)~20	5.0~20.0	4.0	M5	8
		12		13.00~16.00	12~24	5.0~20.0	5.0		
		13	-0.007 -0.020	14.00~18.00	13(14)~26	5.0~20.0	5.5	M8	10
		16		17.00~25.00	16~32	10.0~20.0	7.0		12
		20	22.00~30.00	20~40	10.0~20.0	9.0			

<訂正用>

-0.004
-0.012
-0.005
-0.014
-0.006
-0.017
-0.007
-0.020