

P779 (規格表)

赤枠内 E寸法を修正

■内ねじ

Catalog No.		D寸公差 g6	P 指定0.01mm単位	L 指定1mm単位	B 指定0.5mm単位	E	M (並目)
Type	D						
EHPFM GEHPFM BEHPFM SEHPFM HEHPFM CEHPFM TEHPFM	6	-0.004 -0.012	7.00~10.00	9~12	3.0~12.0	× 4 ×	M3
	8	-0.005	9.00~13.00	12~15	3.0~14.0		5
	10	-0.014	11.00~15.00	13~15	3.0~16.0	6	M5
	12	-0.006 -0.017	13.00~16.00	13~18	3.0~18.0		7
	13		14.00~18.00	17~20	3.0~20.0		
	16	17.00~25.00	17~25	3.0~20.0			
	20	-0.007 -0.020	21.00~30.00	17~32	3.0~20.0		

<訂正用>

5