

- ①スタンダードタイプD3のp6公差訂正
- ②D寸5・6のE寸数値訂正
- ③内ねじ内ねじタイプの価格訂正

■スタンダード

型式		D寸公差			P 選択	L	B	C	ℓ	E	¥単価 1~4口						
Type	形状記号	D	m6	p6							① JPRSB JPRSPB	② GJPRSB GJPRSPB	③ SJPRSB SJPRSPB	④ CJPRSB CJPRSPB	⑤ MJPRSB MJPRSPB	⑥ MGJPRSB MGJPRSPB	⑦ MCJPRSB MCJPRSPB
JPRS GJPRS SJPRS CJPRS  (バフ研磨品) B (m6) PB (p6) MJPRS MGJPRS MCJPRS ①D≧5かつ ②P≧5に適用		3	+0.008 +0.002	+0.012 +0.006	2 3	5	3	0.5	3	320	420	480	530	—	—	—	
		4			2 3 4					350	460	530	580	—	—	—	
		5	+0.012 +0.004	+0.020 +0.012	2 3 4 5					380	500	570	630	490	650	820	
		6			3 4 5 6	10	5	1	4	400	540	600	660	520	700	860	
		8	+0.015 +0.006	+0.024 +0.015	4 5 6 8					420	570	630	690	550	740	900	
		10			6 8 10	15	6	1.5	5	440	590	660	710	570	770	920	
		12			8 10 12					460	620	690	720	600	810	940	
		13	+0.018 +0.007	+0.029 +0.018		12 13	22	8	2	6	480	650	710	790	620	850	1,030
		16			12 13 14 15 16	640					860	960	1,060	830	1,120	1,380	
		20	+0.021 +0.008	+0.035 +0.022		15 16 20	30	10	3	7	810	1,080	1,220	1,330	1,050	1,400	1,730

■内ねじ

型式		D	D寸公差 g6	P 選択	L	B	E	M (径目)	ℓ	¥単価 1~4口							
Type	形状記号									① JPRSTB	② GJPRSTB	③ SJPRSTB	④ CJPRSTB	⑤ MJPRSTB	⑥ MGJPRSTB	⑦ MCJPRSTB	
JPRS GJPRS SJPRS CJPRS  (バフ研磨品) TB MJPRS MGJPRS MCJPRS ①D≧5に適用		6	-0.004	4 5 6	10	5	M3	5	680	910	850	900	880	1,180	1,170		
		6T	-0.012	4 5 6					M2.6	4	680	910	850	900	880	1,180	1,170
		8		6 8					M4	6	680	920	870	910	880	1,200	1,180
		8T	-0.005 -0.014	6 8	15	6	M3	5	8	680	920	870	910	880	1,200	1,180	
		10		8 10						710	960	900	950	920	1,250	1,240	
		12		8 10 12	22	8	6	M5	8	730	980	920	980	950	1,270	1,270	
		13	-0.006 -0.017	12 13						730	980	920	980	950	1,270	1,270	
		16		12 13 14 15 16	30	10	7	M8	12	900	1,220	1,070	1,250	1,170	1,590	1,630	
		20	-0.007 -0.020	15 16 20						1,070	1,440	1,280	1,510	1,390	1,870	1,960	

<訂正用>

①  $\begin{matrix} +0.012 \\ +0.006 \end{matrix}$

②

3
4
5

③

[ 980 | 950 | 1,270 | 1,270 ]

③

③