

## ノブなしタイプM10～12LのL寸数値訂正

型式		ピッチ (細目)	D <sub>1</sub>	B	S min.	L	L <sub>1</sub>	L <sub>2</sub>	L <sub>3</sub>	L <sub>4</sub>	M <sub>2</sub> (並目)	Sw <sub>1</sub>	Sw <sub>2</sub>	R <sub>1</sub>	荷重(N)		質量(g)		¥単価 1～4コ			
Type	M														min.	max.	PXNAN SXNAN	PXNKN SXNKN	PXNAN	SXNAN	PXNKN	SXNKN
PXNAN SXNAN PXNKN SXNKN	8	1.0	11.5	4	4	16	5	14	4	3	10	13	2	3	9	10	15	1,220	1,650	1,270	1,870	
	8L				6										12			1,350	1,840	1,410	2,080	
	10	1.0	13.8	5	5	17	5	15	5	4	12	17	2.5	5	11.5	15	22	1,220	1,650	1,270	1,870	
	10L				8										16			1,350	1,840	1,410	2,080	
	12	1.5	16.2	6	6	20	6	17	6	5	14	19	3	6.5	14.5	25	35	1,300	1,790	1,380	2,060	
	12L				10										20			1,440	1,980	1,530	2,290	
	16	1.5	21.9	8	7	26	8	23	8	6	19	24	4	7.5	18	57	77	1,540	2,420	1,720	2,850	
	16L				12										54			1,710	2,680	1,900	3,160	

kgf=N×0.101972

&lt;訂正用&gt;

L
30
32
32
35
39
44
49
54