

A寸25のF寸数値訂正

■マイクロメータヘッド(XZSG・XYZSG)・送りねじ(XZSCG・XYZSCG)

型式		H		C		K ₁	Q	J	B±S(移動量)		E	F	N	T	T ₁	D	G	P	G ₁	X	d ₁	d ₂	ℓ	付属品(4本) Type M-L
Type	A	XZ軸	XYZ軸	マイクロ メータ	送り ねじ				マイクロ メータ	送り ねじ														
XZSG XZSCG XYZSG XYZSCG	25	24.5	36.5	37	23	10	8.5	6.8	25±3.2	11±3.2	7	9	7	12	3.7	9.3	7	6	10	20	4.2	2.5	2.5	SCB2-4
	40	51	67	58.5	55	14	10.5	11.5	24±6.5	20.3±6.5	12	18.5	5	16	4.5	13	9	10	13	32	6	3.5	3.5	SCB3-6
	50	46	62	58.5	55	19	10.5	11.5	19±6.5	15.3±6.5	12	18.5	20	16	4.5	13	9	10	13	40	6	3.5	3.5	SCB3-6
	60	41	57	58.5	55	24	10.5	11.5	14±6.5	10.3±6.5	12	18.5	21	16	5	13	9	10	13	50	8	4.5	4	SCB4-6
	70	43	61	58.5	55	23.5	11.5	11.5	14.5±6.5	10.8±6.5	12	18.5	12	18	6	13	10	10	14	60	8	4.5	4.5	SCB4-6
	80	40	60	96	55	25	14.5	11.5	43.5±12.5	10±6.5	17	22※	20	20	6.5	18	11	10	16.5	70	8	4.5	5.3	SCB4-6

<訂正用>

F
9
18.5
18.5
18.5
18.5
22※