

赤枠内 表記の修正

Catalog No.		T選択					指定5mm単位 (A≧B)		使用推奨温度	耐熱温度	最小曲げR	面密度
Type	T						A	B	°C	°C	mm	kg/m <sup>2</sup>
FBSKYU	6.5	11.5	16.5	21.5	31.5	50~800	50~500	0~30	70	200*1	3.20*1	
FBSES	1.5							0~30		100	2.70	
FBSYA	3 6 10							0~130		130	12.00*2	
FBSKYKAA	31.5							0~30	70	3.45		
FBSKYKAY	16 26 36							0~70		平面貼り*3	12.75*4	
FBSKYKA	10 20 30 50					0~70	0.75*5					
						50~1000	50~1000					



Order  
注文例

Catalog No. - A - B

FBSKYU16.5 - 105 - 255



Delivery  
出荷日

5 日目発送

- \*1. T=21.5の時
- \*2. T=6の時
- \*3. 曲げる事は可能ですが粘着力が弱くなります。
- \*4. T=36の時
- \*5. T=30の時



Price  
価格

■数量スライド価格 (◎1円未満切り捨て) P.81

数量	1~19	20~49	50~99	100~199	◎表示数量超えは お見積り
値引率	価格表	5%	10%	15%	

Catalog No.		¥単価 1~19枚					
Type	T	B					
		50~100	105~200	205~300	305~400	405~500	
FBSKYU	6.5	50~300	570	870	1,350	—	—
		305~500	700	1,220	2,070	2,150	2,270
		505~800	900	1,720	2,850	2,940	3,050
	11.5	50~300	590	920	1,440	—	—
		305~500	740	1,300	2,220	2,420	2,570
		505~800	950	1,850	3,080	3,160	3,300
	16.5	50~300	600	950	1,540	—	—
		305~500	770	1,370	2,370	2,540	2,620
		505~800	1,020	1,970	3,310	3,440	3,540
	21.5	50~300	620	1,000	1,620	—	—
		305~500	800	1,450	2,520	2,600	2,690
		505~800	1,050	2,100	3,530	3,650	3,760
31.5	50~300	700	1,120	1,800	—	—	
	305~500	900	1,640	2,820	2,970	3,120	
	505~800	1,220	2,390	3,960	4,170	4,370	
FBSES	1.5	50~300	520	750	1,120	1,200	1,300
		305~500	620	1,000	1,650	1,770	1,890
		505~800	790	1,400	2,240	2,330	2,440
FBSYA	3	50~300	570	990	1,690	—	—
		305~500	770	1,490	2,670	2,720	2,770
		505~800	1,050	2,200	3,730	3,740	3,770
	6	50~300	750	1,300	2,220	—	—
		305~500	1,000	1,950	3,500	3,590	3,640
		505~800	1,390	2,900	4,910	4,930	4,960
10	50~300	940	1,640	2,650	—	—	
	305~500	1,250	2,470	4,020	4,400	4,600	
		505~800	1,740	3,650	5,280	5,840	6,280

Catalog No.		¥単価 1~19枚					
Type	T	B					
		50~100	105~200	205~300	305~400	405~500	
FBSKYKAA	31.5	50~300	1,250	2,040	2,910	3,480	3,870
		305~500	1,770	2,940	4,250	5,050	5,600
		505~800	2,560	4,110	5,850	6,770	7,600
		50~300	1,100	1,700	2,370	2,770	3,140
FBSKYKAY	26	305~500	1,510	2,420	3,440	4,020	4,590
		505~800	2,100	3,360	4,700	5,470	6,400
		50~300	1,300	2,000	2,820	3,300	3,730
		305~500	1,800	2,870	4,080	4,770	5,440
36	36	505~800	2,500	3,990	5,590	6,500	7,600
		50~300	1,440	2,220	3,110	3,650	4,130
		305~500	1,990	3,170	4,510	5,280	6,000
		505~800	2,760	4,400	6,170	7,170	8,400

Catalog No.		¥単価 1~19枚					
Type	T	B					
		50~200	205~400	405~600	605~800	805~1000	
FBSKYKA	10	50~400	570	840	1,170	1,500	1,840
		405~700	920	1,340	1,920	2,500	3,100
		705~1000	1,270	1,840	2,480	3,250	3,940
	20	50~400	940	1,350	1,970	2,550	3,170
		405~700	1,550	2,250	3,320	4,370	5,420
		705~1000	2,190	3,170	4,310	5,700	6,990
30	50~400	1,250	1,820	2,650	3,470	4,300	
	405~700	2,120	3,070	4,450	5,890	7,320	
	705~1000	2,970	4,300	5,760	7,700	9,130	
50	50~400	1,950	2,820	4,170	5,500	6,840	
	405~700	3,340	4,820	7,090	9,390	11,700	
	705~1000	4,720	6,840	9,190	12,310	14,940	

<訂正用>

①

指定5mm単位 (A≧B)	
	B

②

305~400	405~500
—	—
2,150	2,270
2,940	3,050
—	—
2,420	2,570
3,160	3,300
—	—
2,540	2,620
3,440	3,540
—	—
2,600	2,690
3,650	3,760
—	—
2,970	3,120
4,170	4,370
1,200	1,300
1,770	1,890
2,330	2,440
—	—
2,720	2,770
3,740	3,770
—	—
3,590	3,640
4,930	4,960
—	—
4,400	4,600
5,840	6,280