

価格の訂正

■寸法選択タイプ

型式 Type	V	D 選択	L 0.5mm 単位	¥単価 1~4コ								
				CLJHJ CLJHK	CLJHM CLJHW	CLJHD	CLJHB	CLJHN	CLJHT	CLJHF	CLJHP	CLJHE
CLJHJ CLJHK CLJHM CLJHW CLJHD CLJHT CLJHB CLJHN CLJHF CLJHP CLJHE	2	(4) 5 6 8 10	10.0 ~ 25.0	290	320	760	270	520	800	1,500	4,000	1,150
	3		25.5 ~ 30.0	320	340	820	300	540	860	2,770	5,530	2,330
	4	(6) 8 10 11 12 13 14 15 16 20 25	10.0 ~ 25.0	290	320	790	270	520	860	3,330	8,500	1,430
			25.5 ~ 50.0	320	340	840	300	540	940	6,770	12,470	2,930
	6	8 10 11 12 13 14 15 16 20 25	10.0 ~ 25.0	320	340	820	300	540	860	3,330	8,500	1,780
			25.5 ~ 50.0	340	370	890	320	570	940	6,770	12,470	3,420
	8	10 11 12 13 14 15 16 20 25 30	10.0 ~ 25.0	360	390	930	340	590	980	4,480	9,830	2,770
			25.5 ~ 50.0	390	410	990	370	610	1,040	8,670	14,620	5,230
			50.5 ~ 75.0	420	460	1,100	400	660	1,160	—	—	—
			75.5 ~ 100.0	510	550	1,310	490	750	1,380	—	—	—
	10	12 13 14 15 16 20 25 30	10.0 ~ 25.0	400	430	960	380	630	1,010	4,620	10,130	2,860
			25.5 ~ 50.0	560	580	1,030	540	780	1,080	8,940	15,060	5,390
			50.5 ~ 75.0	630	680	1,140	610	880	1,200	—	—	—
			75.5 ~ 100.0	760	850	1,360	740	1,050	1,430	—	—	—
	12	15 16 20 25 30	10.0 ~ 25.0	490	530	1,030	470	780	1,080	7,300	15,380	5,180
			25.5 ~ 50.0	850	880	1,390	820	1,180	1,460	9,800	20,600	6,700
			50.5 ~ 75.0	1,010	1,090	1,620	980	1,410	1,700	—	—	—
			75.5 ~ 100.0	1,280	1,430	2,030	1,240	1,770	2,140	—	—	—
	15	20 25 30	10.0 ~ 25.0	460	490	1,000	440	690	1,050	4,760	10,440	2,950
			25.5 ~ 50.0	620	650	1,060	600	850	1,120	9,210	15,520	5,560
			50.5 ~ 75.0	760	800	1,180	740	1,000	1,240	—	—	—
			75.5 ~ 100.0	930	1,020	1,410	910	1,220	1,480	—	—	—
	16	35 40 50	10.0 ~ 25.0	520	550	1,150	490	770	1,210	8,050	16,250	5,700
			25.5 ~ 50.0	900	940	1,570	870	1,230	1,650	10,480	21,720	7,270
50.5 ~ 75.0			1,070	1,130	1,920	1,050	1,410	2,020	—	—	—	
75.5 ~ 100.0			1,350	1,480	2,380	1,320	1,770	2,500	—	—	—	
20	35 40 50	10.0 ~ 25.0	510	530	1,050	490	730	1,110	5,000	10,970	3,100	
		25.5 ~ 50.0	680	730	1,120	660	930	1,180	9,680	16,300	5,840	
		50.5 ~ 75.0	850	930	1,240	830	1,130	1,310	—	—	—	
		75.5 ~ 100.0	1,060	1,140	1,480	1,040	1,340	1,560	—	—	—	
25	40 50	10.0 ~ 25.0	550	570	1,270	530	790	1,340	8,550	17,000	6,120	
		25.5 ~ 50.0	950	1,020	1,750	920	1,300	1,840	11,050	22,550	7,620	
		50.5 ~ 75.0	1,130	1,240	2,220	1,110	1,510	2,340	—	—	—	
		75.5 ~ 100.0	1,420	1,530	2,720	1,400	1,800	2,860	—	—	—	
30	40 50	10.0 ~ 25.0	580	600	1,330	560	830	—	—	—	—	
		25.5 ~ 50.0	1,000	1,070	1,830	970	1,360	—	—	—	—	
		50.5 ~ 75.0	1,190	1,310	2,330	1,170	1,600	—	—	—	—	
		75.5 ~ 100.0	1,500	1,620	2,850	1,480	1,910	—	—	—	—	
40	50	10.0 ~ 25.0	630	660	1,110	610	860	1,170	5,250	11,520	3,260	
		25.5 ~ 50.0	800	930	1,180	780	1,130	1,240	10,170	17,120	6,140	
		50.5 ~ 75.0	970	1,060	1,310	950	1,260	1,380	—	—	—	
		75.5 ~ 100.0	1,190	1,310	1,560	1,170	1,510	1,640	—	—	—	
50	60	10.0 ~ 25.0	580	610	1,690	560	790	1,780	18,570	17,680	7,100	
		25.5 ~ 50.0	1,000	1,160	2,340	970	1,410	2,460	24,470	23,380	8,830	
		50.5 ~ 75.0	1,190	1,300	2,620	1,170	1,550	2,760	—	—	—	
		75.5 ~ 100.0	1,500	1,650	3,230	1,470	1,900	3,400	—	—	—	
60	60	10.0 ~ 25.0	610	640	1,770	590	830	—	—	—	—	
		25.5 ~ 50.0	1,060	1,230	2,450	1,030	1,500	—	—	—	—	
		50.5 ~ 75.0	1,250	1,370	2,750	1,230	1,630	—	—	—	—	
		75.5 ~ 100.0	1,580	1,740	3,390	1,550	2,000	—	—	—	—	
70	60	10.0 ~ 25.0	610	640	1,810	590	830	1,900	19,820	18,570	7,620	
		25.5 ~ 50.0	1,050	1,220	2,430	1,020	1,490	2,560	26,050	24,470	9,420	
		50.5 ~ 75.0	1,250	1,370	2,720	1,230	1,630	2,860	—	—	—	
		75.5 ~ 100.0	1,580	1,740	3,330	1,550	2,000	3,500	—	—	—	
80	60	10.0 ~ 25.0	650	680	1,900	590	880	—	—	—	—	
		25.5 ~ 50.0	1,120	1,300	2,550	1,020	1,590	—	—	—	—	
		50.5 ~ 75.0	1,320	1,450	2,850	1,230	1,730	—	—	—	—	
		75.5 ~ 100.0	1,660	1,830	3,500	1,550	2,100	—	—	—	—	