

価格表の寸範囲訂正

■角シム

A	B	¥単価 1~4コ										
		ASAFR・ASACR			ASAFB・ASACB				ASAFS・ASACS			
		T0.1~0.5	T1.0	T2.0	T0.05	T0.1~0.5	T1.0	T2.0~3.0	T0.05	T0.1~0.5	T1.0	T2.0~3.0
16~50	10~50	750	760	770	900	860	860	890	780	730	750	810
	51~100	760	780	790	1,040	860	870	1,020	900	740	780	880
	101~150	770	790	800	1,220	880	900	1,160	1,050	780	790	1,010
51~70	10~50	760	770	780	910	860	860	940	840	740	790	870
	51~100	770	780	790	1,110	870	890	1,100	1,100	770	840	1,080
	101~150	790	790	800	1,330	890	930	1,270	1,180	810	900	1,140
71~100	10~50	770	780	790	960	860	870	1,010	970	740	790	1,020
	51~100	780	790	800	1,230	890	920	1,220	1,180	800	860	1,180
	101~150	790	800	820	1,500	920	970	1,440	1,310	860	940	1,260
101~130	10~50	770	780	790	1,000	880	910	1,050	980	760	780	1,030
	51~100	780	790	800	1,310	900	950	1,310	1,220	800	850	1,220
	101~150	800	800	820	1,660	950	1,000	1,620	1,570	860	940	1,510
131~150	10~50	770	780	790	1,050	880	910	1,100	1,010	780	790	1,060
	51~100	780	790	810	1,400	920	970	1,400	1,260	860	880	1,260
	101~150	800	820	840	1,810	970	1,030	1,750	1,590	890	970	1,520

A	B	¥単価 1~4コ										
		ASFFR・ASFCR			ASFFB・ASFCB				ASFFS・ASFCS			
		T0.1~0.5	T1.0	T2.0	T0.05	T0.1~0.5	T1.0	T2.0~3.0	T0.05	T0.1~0.5	T1.0	T2.0~3.0
16~50	10~50	930	940	940	1,080	1,000	1,030	1,170	980	840	890	1,030
	51~100	950	960	960	1,290	1,010	1,030	1,310	1,160	860	930	1,150
	101~150	960	970	980	1,490	1,020	1,040	1,470	1,300	890	960	1,290
51~70	10~50	930	940	950	1,140	1,010	1,030	1,230	1,020	850	890	1,070
	51~100	950	960	980	1,380	1,020	1,040	1,410	1,230	880	960	1,230
	101~150	960	970	1,000	1,610	1,030	1,050	1,590	1,430	890	1,010	1,390
71~100	10~50	940	950	950	1,220	1,010	1,030	1,310	1,100	860	930	1,150
	51~100	960	970	1,000	1,520	1,030	1,050	1,550	1,340	890	960	1,360
	101~150	970	970	1,010	1,820	1,040	1,090	1,810	1,630	900	1,060	1,580
101~130	10~50	950	960	960	1,320	1,030	1,030	1,410	1,170	870	960	1,230
	51~100	960	970	1,010	1,660	1,050	1,070	1,700	1,480	900	1,020	1,480
	101~150	970	970	1,020	2,070	1,080	1,120	2,060	1,840	930	1,130	1,810
131~150	10~50	950	960	1,000	1,370	1,030	1,030	1,470	1,220	890	970	1,290
	51~100	960	970	1,020	1,780	1,050	1,070	1,810	1,580	930	1,020	1,580
	101~150	970	1,000	1,080	2,200	1,080	1,150	2,220	2,020	980	1,130	1,940

A	B	¥単価 1~4コ										
		ASCFR・ASCCR			ASCFB・ASCCB				ASCFs・ASCCs			
		T0.1~0.5	T1.0	T2.0	T0.05	T0.1~0.5	T1.0	T2.0~3.0	T0.05	T0.1~0.5	T1.0	T2.0~3.0
16~50	10~50	940	950	950	1,090	1,010	1,040	1,180	1,000	860	910	1,060
	51~100	960	970	970	1,310	1,020	1,040	1,320	1,190	880	950	1,180
	101~150	970	980	990	1,510	1,030	1,050	1,490	1,340	910	980	1,320
51~70	10~50	940	950	960	1,150	1,020	1,040	1,240	1,050	870	910	1,100
	51~100	960	970	990	1,390	1,030	1,050	1,420	1,260	900	980	1,260
	101~150	970	980	1,010	1,620	1,040	1,070	1,600	1,470	910	1,030	1,430
71~100	10~50	950	960	960	1,230	1,020	1,040	1,320	1,130	880	950	1,180
	51~100	970	980	1,010	1,540	1,040	1,070	1,560	1,380	910	980	1,390
	101~150	980	980	1,020	1,840	1,050	1,100	1,820	1,670	930	1,080	1,620
101~130	10~50	960	970	970	1,330	1,040	1,040	1,420	1,200	890	980	1,260
	51~100	970	980	1,020	1,680	1,070	1,080	1,720	1,520	930	1,050	1,520
	101~150	980	980	1,030	2,090	1,090	1,130	2,080	1,890	950	1,160	1,850
131~150	10~50	960	970	1,010	1,380	1,040	1,040	1,490	1,250	910	990	1,320
	51~100	970	980	1,030	1,800	1,070	1,080	1,820	1,620	950	1,050	1,620
	101~150	980	1,020	1,090	2,230	1,090	1,160	2,250	2,070	1,000	1,160	1,990

<訂正用> T0.1~0.5 T1.0 T2.0 T0.05 T0.1~0.5 T1.0 T2.0~3.0 T0.05 T0.1~0.5

T0.1~0.5 T1.0 T2.0 T0.05 T0.1~0.5 T1.0 T2.0~3.0 T0.05 T0.1~0.5