

## 価格の訂正

## ■六角穴付樹脂ボルト

型式 Type M-L	M × P	A	E	B	¥単価						*数量
					*数量未満			*数量以上			
					REN	PPS	PEK	REN	PPS	PEK	
REN 3-6 PPS 8 PEK 10	3 × 0.5	5.5	3	2.5	28	27	36	25	26	34	100
12					30	29	38	27	28	36	
15					34	32	40	31	30	38	
20					40	38	42	36	36	40	
					48	46	60	43	44	57	
					54	51	80	49	48	76	
REN 4-6 PPS 8 PEK 10	4 × 0.7	7	4	3	34	32	52	31	30	49	100
12					38	36	56	34	34	53	
15					40	38	58	36	36	55	
20					48	46	62	43	44	59	
					54	51	76	49	48	72	
					60	57	80	54	54	76	
REN 5-10 PPS 12 PEK 15	5 × 0.8	8.5	5	4	60	57	90	54	54	86	100
20					64	63	110	58	60	105	
25					76	80	120	68	76	114	
30					90	93	140	81	88	133	
					110	120	160	99	118	152	
					140	160	220	126	150	209	
REN 6-15 PPS 20 PEK 25	6 × 1.0	10	6	5	110	120	190	99	118	181	100
30					140	160	220	126	150	209	
40					170	190	290	153	180	276	
					200	240	330	180	220	314	
					230	290	340	207	270	323	
REN 8-15 PPS 20 PEK 25	8 × 1.25	13	8	6	170	240	420	153	220	399	50
30					210	260	440	189	250	418	
40					250	310	480	225	290	456	
					290	380	520	261	360	494	
					330	480	560	297	450	532	
REN 10-15 20 25 30 35 40	10 × 1.5	16	10	8	270			243			50
					300			270			
					330			297			
					360			324			
					390			351			
					400			360			
REN 12-20 25 30 35 40	12 × 1.75	18	12	10	380			342			50
					420			378			
					460			414			
					490			441			
					520			468			

&lt;訂正用&gt;

[118]

[118]