

E形状部 数値を一部変更

■継手寸法表

No.	A形状			B形状				C形状					D形状		E形状	
	A	B	H	A	B	H ₁	H ₂	A	B	H ₁	H ₂	H ₃	A	B	A	B
8A	34.0	27.5	17	34.0	27.5	38	55	—	—	—	—	—	—	—	—	—
10A	34.0	27.5	17	34.0	27.5	38	55	—	—	—	—	—	—	—	—	—
15A	34.0	27.5	17	34.0	27.5	38	55	—	—	—	—	—	—	—	—	—
1S	50.5	43.4	21	50.5	43.4	34	55	50.5	43.4	36.8	15.8	43.9	—	—	—	—
1.5S	50.5	43.4	21	50.5	43.4	49	70	50.5	43.4	44.7	23.7	49.5	50.5	43.4	50.5	43.4
2S	64.0	56.4	21	64.0	56.4	61	82	64.0	56.4	52.6	31.6	59.8	50.5	43.4	50.5	43.4
2.5S	77.5	70.4	21	77.5	70.4	84	105	77.5	70.4	63.0	42.0	71.9	64.0	56.4	64.0	56.4
3S	91.0	83.4	21	91.0	83.4	89	110	91.0	83.4	73.6	52.6	84.2	77.5	70.4	77.5	70.4

<訂正用>

50.5

50.5

64.0

77.5