

P1522 (注釈)

注文例・出荷日の場所を注釈として記載

Catalog No. Type	呼び D	L <sub>1</sub>	L <sub>2</sub>	A	B	C	E	F	N	ねじサイズ M	2面幅 H	質量 (g)	¥単価		
													1~9コ	10~50	
UNSTLT	4	M5	22.5	19	4	16	10	4.2	11	7.5	M5×0.8	10	11.5	490	460
		1	26.5	19	8	16	10	4.2	11	7.5	R1/8	10	13	430	400
		2	30	19	11	16	10	4.2	11	7.5	R1/4	14	20	450	420
	6	M5	25	21.5	4	17.5	12.5	4.2	13.5	8.5	M5×0.8	14	20.5	540	510
		1	30	21.5	8	17.5	12.5	4.2	13.5	8.5	R1/8	14	22.5	480	450
		2	33	21.5	11	17.5	12.5	4.2	13.5	8.5	R1/4	14	26	500	470
		3	34.5	21.5	12	17.5	12.5	4.2	13.5	8.5	R3/8	17	34	570	540
	8	1	32.5	24	8	19	14.5	4.2	15.5	9.5	R1/8	17	29.5	530	500
		2	35.5	24	11	19	14.5	4.2	15.5	9.5	R1/4	17	32.5	550	520
		3	37	24	12	19	14.5	4.2	15.5	9.5	R3/8	17	38	580	550
	10	2	39.5	27.5	11	21.5	17.5	4.2	18.5	13	R1/4	19	46.5	680	640
		3	41	27.5	12	21.5	17.5	4.2	18.5	13	R3/8	19	52	720	680
4		44	27.5	15	21.5	17.5	4.2	18.5	13	R1/2	22	65.5	790	750	
12	2	41.5	30	11	23	20	4.2	21	14	R1/4	22	60	790	750	
	3	43	30	12	23	20	4.2	21	14	R3/8	22	68	810	760	
	4	46	30	15	23	20	4.2	21	14	R1/2	22	77	860	810	

⊗水の使用不可 ⊕注文例・出荷日はP.1521をご参照ください。⊙表示数量超えはお見積り

<訂正用>

⊗水の使用不可 ⊕注文例・出荷日はP.1521をご参照ください。⊙表示数量超えはお見積り