

- ①HOTAM・HOATの呼び径113・125・150のA<sub>1</sub>寸数値訂正
- ②HOAYEM・HOAYEの図面訂正
- ③HOAYEM・HOAYEのL寸数値訂正

■アルミダクトホース用  
—T型—

Type	M材質	S表面処理
HOATM	SS400	アクリル焼付け塗装
HOAT	SUS304	—

RoHS

型式		D	L	A <sub>1</sub>	t	¥単価 1~4口	
Type	呼び径					HOATM	HOAT
HOATM HOAT	38	38	100	50	1.2	2,500	5,430
	50	49	120	60	1.5	2,850	6,900
	65	63.5	135	68	2	3,200	8,400
	75	75	145	72		3,910	9,480
	100	98	180	90		6,410	12,270
	113	112	180	100		7,770	14,250
	125	124	200	110		8,930	16,570
	150	149	240	120		10,430	21,780

■アルミダクトホース用  
—変則Y型—

Type	M材質	S表面処理
HOAHYM	SS400	アクリル焼付け塗装
HOAHY	SUS304	—

RoHS

型式		D	L	A <sub>1</sub>	t <sub>1</sub>	¥単価 1~4口	
Type	呼び径					HOAHYM	HOAHY
HOAHYM HOAHY	38	38	114	30	1.2	4,180	8,360
	50	49	141	36	1.5	4,430	9,030
	65	63.5	172	41	2	4,980	10,060
	75	75	194	44		7,270	13,330
	100	98	243	52		8,710	16,180
	113	112	278	60		10,230	18,600
	125	124	305	65		11,530	22,370
150	149	350	70	15,860		29,980	

■アルミダクトホース用  
—ダンパー—

Type	M材質	S表面処理
HOANPM	SS400	アクリル焼付け塗装
HOANP	SUS304	—

型式		D	A	B	C	D <sub>1</sub>	P.C.D.	d <sub>1</sub>	¥単価 1~4口	
Type	呼び径								HOANPM	HOANP
HOANPM HOANP	38	38	99	41	75	66	52	6.6	7,840	15,720
	50	49				79	65		8,070	16,460
	65	63.5				91.5	77.5		8,300	16,610
	75	75	119	51	111	94	8,100		16,920	
	100	98			136	119	8,400		17,380	
	125	124			168	148	13,310		24,950	
	150	149			193	173	17,140		33,550	

■アルミダクトホース用  
—異形Y型—

Type	M材質	S表面処理
HOAYEM	SS400	アクリル焼付け塗装
HOAYE	SUS304	—

RoHS

型式		D <sub>1</sub>	D <sub>2</sub>	L	t <sub>1</sub>	t <sub>2</sub>	¥単価 1~4口	
Type	呼び径						HOAYEM	HOAYE
HOAYEM HOAYE	50	49	38	80	1.5	1.2	4,300	8,890
	65	63.5	49	85	2	1.5	5,000	9,490
	75	75	63.5	88		7,420	14,150	
	100	98	75	100		9,450	17,240	
	113	112	98	105		10,460	19,700	
	125	124	112	110		11,980	24,450	
	150	149	124	120		16,010	32,980	

■アルミダクトホース用  
—フランジ—

Type	M材質	S表面処理
HOAJ	SUS304	—

RoHS

型式		t	D <sub>1</sub>	P. C. D.	d <sub>1</sub>	¥単価 1~4口	
Type	呼び径					HOAJ	
HOAJ	38	2	66	52	6.6	1,000	
	50		79	65		1,110	
	65		91.5	77.5		1,240	
	75		111	94	9	1,400	
	100		136	119		1,460	
	113		152	134		1,630	
	125		168	148		1,940	
150	193	173	2,500				

<訂正用>

①

A <sub>1</sub>
50
60
68
72
90
100
110
120

②

Type	M材質	S表面処理
HOAYEM	SS400	アクリル焼付け塗装
HOAYE	SUS304	—

③

L
80
85
88
100
105
110
120