

B寸選択タイプはDH7指定不可です。

型式 Type	M-Pitch	B 選択	DH7	U	A	L	T	¥単価 1~4コ						
								凸型タイプ			凹型タイプ			
								NJSB	NJSM	NJSS	NJTB	NJTM	NJTS	
(凸型) NJSB NJSM NJSS (凹型) NJTB NJTM NJTS	3-0.5	4・5	4	10	26	20	10	1,200	1,330	2,170	1,200	1,330	2,170	
	4-0.7	5・6						1,200	1,330	2,170	1,200	1,330	2,170	
	5-0.8	5・6						1,280	1,410	2,280	1,280	1,410	2,280	
	6-1.0	4・6	5		15	31	25	12	1,280	1,410	2,280	1,280	1,410	2,280
	8-1.0	5・8							1,360	1,500	2,420	1,360	1,500	2,420
	8-1.25	5・8							1,360	1,500	2,420	1,360	1,500	2,420
	10-1.25	6・10	8	20		43	35	16	1,510	1,660	2,670	1,510	1,660	2,670
	10-1.5	6・10							1,510	1,660	2,670	1,510	1,660	2,670
	12-1.25	8・10							1,660	1,830	2,970	1,660	1,830	2,970
	12-1.5	8・10	10		25	50	40	22	1,660	1,830	2,970	1,660	1,830	2,970
	14-1.5	10・12							1,660	1,830	2,970	1,660	1,830	2,970
	16-1.5	10・12							1,960	2,170	3,500	1,960	2,170	3,500
	16-1.5	10・12	12	30		62	50	25	1,960	2,170	3,500	1,960	2,170	3,500
	18-1.5	10・12							1,960	2,170	3,500	1,960	2,170	3,500
	18-1.5	12・14							2,110	2,330	3,760	2,110	2,330	3,760
						67	55	28	1,960	2,170	3,500	1,960	2,170	3,500
						69			2,110	2,330	3,760	2,110	2,330	3,760

<訂正用>

