

歯数16の枠を削除

■MXLタイプ (センターベアリングタイプ)

片持ちピンはP.559~580をご参照ください。

Catalog No.			P.D.	O.D.	F	E	A	W	S	ベアリング寸法				使用止め輪		¥単価 1~4コ					
Type	歯数	対応ベルト								No.	d	D	B	A [□] TF MATF SATF	BATF	AATF	AKTF	ANTF	BATF	MATF	SATF
AATF AKTF ANTF BATF MATF SATF	18	MXL019	12.94	12.43	18	11	6	10	3	693ZZ×1	3	8	4	RTWS8	RTWN8	2,110	2,320	2,530	—	—	—
	20	MXL019	12.94	12.43	18	11	6	10	3	693ZZ×1	3	8	4	RTWS8	RTWN8	2,110	2,320	2,530	—	—	—
	22	MXL019	14.23	13.72	18	11	6	10	3	693ZZ×1	3	8	4	RTWS8	RTWN8	2,190	2,400	2,620	—	—	—
	24	MXL019	15.52	15.02	20	13	6	10	3	693ZZ×1	3	8	4	RTWS8	RTWN8	2,230	2,450	2,670	—	—	—
	30	MXL019	19.40	18.90	25	16	6	10	3	695ZZ×1	5	13	4	RTWS13	RTWN13	2,280	2,500	2,730	—	—	—
	36	MXL019	23.29	22.78	28	18	6	10	3	695ZZ×1	5	13	4	RTWS13	RTWN13	2,380	2,610	2,850	—	—	—
	40	MXL019	25.87	25.36	30	20	6	10	2.5	696ZZ×1	6	15	5	RTWS15	RTWN15	2,410	2,650	2,890	—	—	—
		7.5					11.5	3.25	2,410							2,650	2,890	2,340	2,610	3,650	
		11					15	5	2,410							2,650	2,890	2,340	2,610	4,460	
	50	MXL019	32.34	31.84	35	25	6	10	2	698ZZ×1	8	19	6	RTWS19	RTWN19	2,550	2,800	3,060	—	—	—
		7.5					11.5	2.75	2,580							2,830	3,090	2,480	2,750	—	
		11					15	4.5	3,170							3,480	3,800	3,020	3,290	—	
	60	MXL019	38.81	38.30	44	32	6	10	2	6900ZZ×1	10	22	6	RTWS22	RTWN22	2,660	2,920	3,190	—	—	—
		7.5					11.5	2.75	2,700							2,970	3,240	2,600	2,870	—	
11		15					4.5	3,860	4,240							4,630	3,790	4,060	—		

<訂正用>

■MXLタイプ (センターベアリングタイプ)

片持ちピンはP.559~580をご参照ください。

Catalog No.			P.D.	O.D.	F	E	A	W	S	ベアリング寸法				使用止め輪		¥単価 1~4コ					
Type	歯数	対応ベルト								No.	d	D	B	A [□] TF MATF SATF	BATF	AATF	AKTF	ANTF	BATF	MATF	SATF
AATF AKTF ANTF BATF MATF SATF	20	MXL019	12.94	12.43	18	11	6	10	3	693ZZ×1	3	8	4	RTWS8	RTWN8	2,110	2,320	2,530	—	—	—
	22	MXL019	14.23	13.72	18	11	6	10	3	693ZZ×1	3	8	4	RTWS8	RTWN8	2,190	2,400	2,620	—	—	—
	24	MXL019	15.52	15.02	20	13	6	10	3	693ZZ×1	3	8	4	RTWS8	RTWN8	2,230	2,450	2,670	—	—	—
	30	MXL019	19.40	18.90	25	16	6	10	3	695ZZ×1	5	13	4	RTWS13	RTWN13	2,280	2,500	2,730	—	—	—
	36	MXL019	23.29	22.78	28	18	6	10	3	695ZZ×1	5	13	4	RTWS13	RTWN13	2,380	2,610	2,850	—	—	—
	40	MXL019	25.87	25.36	30	20	6	10	2.5	696ZZ×1	6	15	5	RTWS15	RTWN15	2,410	2,650	2,890	—	—	—
		7.5					11.5	3.25	2,410							2,650	2,890	2,340	2,610	3,650	
		11					15	5	2,410							2,650	2,890	2,340	2,610	4,460	
	50	MXL019	32.34	31.84	35	25	6	10	2	698ZZ×1	8	19	6	RTWS19	RTWN19	2,550	2,800	3,060	—	—	—
		7.5					11.5	2.75	2,580							2,830	3,090	2,480	2,750	—	
		11					15	4.5	3,170							3,480	3,800	3,020	3,290	—	
	60	MXL019	38.81	38.30	44	32	6	10	2	6900ZZ×1	10	22	6	RTWS22	RTWN22	2,660	2,920	3,190	—	—	—
		7.5					11.5	2.75	2,700							2,970	3,240	2,600	2,870	—	
		11					15	4.5	3,860							4,240	4,630	3,790	4,060	—	