

F寸法の数値を一部変更

Catalog No.		質量 g	A	B	T		E	N	F	W	C	適用ボルト・ナット				¥単価			
Type	No.				SPHC	SUS						SPHC		SUS304		1~99コ		100~	
HPTLS SHPTLS (ステンレス)	5	46	85	—	3.2	2	18	5.5	10	28	3	M5-8	M5	4	4	1~99コ	100~	1~99コ	100~
	6	92				3	28	6.6				M6-10	M6			180	175	200	195
	8*	89				3	28	9				M8-15	M8			197	192	220	210
HPTTS SHPTTS (ステンレス)	5	52	100	90	3.2	2	18	5.5	10	30	3	M5-8	M5	4	4	1~99コ	100~	1~99コ	100~
	6	106				3	28	6.6				M6-10	M6			190	185	210	200
	8*	103				3	28	9				M8-15	M8			197	192	230	220
HPTPS* SHPTPS* (ステンレス)	5	50	80	130	—	2	18	5.5	30	3	3	M5-8	M5	6	6	—	—	310	295
	6	140	100	150	3.2	—	28	6.6	25	5	5	M6-10	M6			246	236	—	—
	8*	135	—	—	—	—	28	9	20	3	3	M8-15	M8			—	—	—	—
HPTLD	5	81	80	—	2.3	—	38	5.5	9	20	3	M5-8	M5	8	8	290	280	—	—
	6	178	120	—	—	—	58	6.6	14	30	5	M6-10	M6			420	400	—	—
	8-45	445	160	—	3.2	—	78	9	19	40	5	M8-15	M8			490	470	—	—
HPTTD	5	97	110	80	2.3	—	38	5.5	9	20	3	M5-8	M5	8	8	290	280	—	—
	6	217	150	120	—	—	58	6.6	14	30	5	M6-10	M6			420	400	—	—
	8-45	514	200	160	3.2	—	78	9	19	40	5	M8-15	M8			600	570	—	—
HPTGS	5	64	135	18	2.3	—	100	5.5	7	20	3	M5-8	M5	4	4	140	135	—	—
	6	213	205	28	3.2	—	150	7	12.5	30	5	M6-10	M6			170	165	—	—
	8*	560	275	38	4.5	—	200	9	17.5	40	5	M8-15	M8			250	240	—	—
SHPTCUL (ステンレス)	5	95	100	18	—	2	9	5.5	19	63	2	M5-8	M5	4	4	—	—	680	650
	6	150	120	26	—	3	13	7	25	69	2	M6-10	M6			—	—	710	675
	8*	360	150	36	—	3	18	9	37.5	76.5	3	M8-15	M8			—	—	870	830

⑧*は8—45と兼用 ⑨HPTPSは6.8のみ、SHPTPSは5のみとなります。

<訂正用>

F
10
10
10
9
14
19
21.5
9
14
19
21.5
7
12.5
17.5
19
25
37.5