

モジュール1.0-15はキー溝穴+タップ選択不可

モジュール	歯数	¥単価 1~10コ								
		丸穴			丸穴+タップ			キー溝穴+タップ		
		HGEAHB	HGEAHBB	HGEAHBG	HGEAB	HGEABB	HGEABG	HGEAKB	HGEAKBB	HGEAKBG
1.0	15	1,600	1,760	1,920	1,720	1,890	2,070	—	—	—
	20	1,980	2,180	2,370	2,070	2,280	2,490	2,160	2,380	2,590
	30	2,380	2,610	2,850	2,500	2,750	2,990	2,580	2,840	3,100
	40	3,010	3,310	3,610	3,130	3,440	3,750	3,210	3,540	3,860
15	15	1,710	1,890	2,070	1,810	1,990	2,170	1,830	2,010	2,200
	20	2,210	2,430	2,650	2,300	2,530	2,760	2,330	2,560	2,790
	30	2,330	2,560	2,790	2,450	2,690	2,940	2,470	2,720	2,970
	40	3,270	3,600	3,920	3,390	3,730	4,060	3,420	3,770	4,110
2.0	15	2,130	2,340	2,550	2,190	2,410	2,630	2,300	2,540	2,760
	20	2,590	2,850	3,110	2,670	2,940	3,210	2,810	3,090	3,370
	30	3,700	4,070	4,440	3,810	4,190	4,570	4,000	4,400	4,800
	40	5,110	5,620	6,130	5,270	5,800	6,320	5,530	6,080	6,640

④ 表示数量超えはお見積り

&lt;訂正用&gt;

キー溝穴+タップ		
HGEAKB	HGEAKBB	HGEAKBG
—	—	—
2,160	2,380	2,590
2,580	2,840	3,100
3,210	3,540	3,860
1,830	2,010	2,200
2,330	2,560	2,790
2,470	2,720	2,970
3,420	3,770	4,110
2,300	2,540	2,760
2,810	3,090	3,370
4,000	4,400	4,800
5,530	6,080	6,640