

A・B寸法の選択最小値を変更

Price
価格

■数量スライド価格 (◎1円未満切り捨て) P.81

数量	1~4	5~9	10~19	20~49
値引率	価格表	5%	10%	15%

◎表示数量超えは
お見積り

Type	指定1mm単位		D1		D2		D3			D4		D5				
	A	B	T=0.5	T=0.8	T=0.5	T=0.8	T=1.0	T=1.0	T=1.2	T=1.6	T=1.0	T=1.2	T=1.6	T=1.0	T=1.2	T=1.6
PMSF	50~200	50~200	2,040	2,170	1,930	1,960	1,990	1,430	1,450	1,490	1,430	1,450	1,480	1,420	1,440	1,470
		201~300	2,690	2,880	2,530	2,570	2,600	1,900	1,940	2,000	1,900	1,940	1,980	1,900	1,940	1,970
	301~500	201~300	3,540	3,830	3,300	3,360	3,400	2,560	2,630	2,720	2,560	2,630	2,690	2,560	2,610	2,670
		50~200	3,990	4,300	3,730	3,790	3,860	2,870	2,940	3,030	2,870	2,940	3,000	2,850	2,920	2,980
		201~300	5,240	5,720	4,850	4,950	5,040	3,920	4,020	4,160	3,920	4,020	4,110	3,900	3,990	4,090
		301~400	6,490	7,130	5,970	6,100	6,230	4,980	5,100	5,290	4,970	5,100	5,230	4,940	5,060	5,190
	401~500	7,740	8,540	7,090	7,250	7,400	6,020	6,180	6,420	6,020	6,180	6,340	5,980	6,140	6,300	

Type	指定1mm単位		D1		D2		D3			D4		D5		
	A	B	T=0.5	T=0.8	T=1.0	T=1.0	T=1.2	T=1.5	T=1.0	T=1.2	T=1.5	T=1.0	T=1.2	T=1.5
PMUF	50~200	50~200	2,670	3,190	2,570	1,720	1,750	1,810	1,740	1,790	1,850	1,650	1,730	1,810
		201~300	3,550	4,330	3,400	2,260	2,390	2,480	2,380	2,450	2,530	2,230	2,350	2,480
	301~500	201~300	4,720	5,880	4,490	3,090	3,280	3,410	3,270	3,380	3,500	3,050	3,220	3,410
		50~200	5,330	6,620	5,070	3,610	3,820	3,970	3,810	3,940	4,070	3,560	3,760	3,970
		201~300	7,040	8,980	6,660	4,770	5,080	5,300	5,060	5,250	5,440	4,690	4,980	5,300
		301~400	8,760	11,300	8,250	6,100	6,520	6,810	6,480	6,740	7,000	6,000	6,390	6,810
	401~500	10,480	13,700	9,830	7,410	7,940	8,300	7,900	8,220	8,540	7,290	7,770	8,300	

<訂正用>

指定1mm単位	
A	B
50~200	50~200
201~300	50~200
	201~300
301~500	50~200
	201~300
	301~400
	401~500
指定1mm単位	
A	B
50~200	50~200
201~300	50~200
	201~300
301~500	50~200
	201~300
	301~400
	401~500