

P2240 (規格表)

参考許容荷重kN変更

Catalog No.		T	参考許容荷重kN	質量(g)	¥単価1~9コ	
Type	D				SEPLC	SEPLCS
SEPLC SEPLCS (ステンレス)	60	20	5.6	360	180	1,230
		30	14.8	560	260	1,610
	80	20	5.6	600	310	1,890
		30	14.8	990	450	2,320
		50	46.2	1720	740	3,560
	100	20	5.6	950	470	2,570
		30	14.8	1560	690	3,000
		50	46.2	2680	1,140	—

Catalog No.		T	参考許容荷重kN	質量(g)	¥単価1~9コ	
Type	D				SEPLB	SEPLBS
SEPLB SEPLBS (ステンレス)	80	20	10.8	880	400	2,570
		30	24.5	1310	515	3,820
		50	68.5	2260	550	5,950
	100	20	10.8	1350	620	4,030
		30	24.5	2050	650	5,580
		50	68.6	3400	690	8,640
	150	20	10.8	3210	760	—
		30	24.5	4620	795	—

Catalog No.		T	K	d	W	h	参考許容荷重kN	質量(g)	¥単価1~9コ
Type	D								
SEPFC (厚型タイプ)	80	60	30	20	60	30	10	1460	2,800
	100	80	40			38		2150	3,450

kgf(荷重) = N × 0.101972

<訂正用>

20	5.6	950
30	14.8	1560
50	46.2	2680