

赤枠内 内容を修正

■並級・フリーサイズ

Catalog No.		指定1mm単位			T 寸法 公差	¥単価 1~4枚						
Type	T	D	d	D50 200		D201 300	D301 400	D401 500	D501 600	D601 700	D701 800	
ENPM (SS400)	8~9	50~200	0~50	±0.2	4,160	—	—	—	—	—	—	
	10	50~600	0~100		4,160	6,140	9,120	13,760	17,780	—	—	
	11~15				4,570	7,370	11,550	17,970	23,760	—	—	
	16~20	100~800	0~100		4,840	7,730	12,570	18,750	26,060	35,540	45,760	
	21~25				5,240	8,420	13,260	20,500	27,360	37,200	47,180	
26~30	5,760			9,120	14,450	22,080	29,370	41,620	53,460			
ENPN (A5082P)	8~9	50~200	0~50	±0.2	5,430	—	—	—	—	—		
	10	50~600	0~100	±0.6	4,370	6,480	9,590	14,480	18,710	29,400	36,180	
	11~14			±0.2	6,210	9,810	15,530	22,880	30,170	48,150	61,800	
	15	100~800	0~100	±0.7	5,000	7,900	12,510	18,430	24,300	38,780	48,290	
	16~19			±0.2	8,070	12,440	19,160	27,690	37,190	50,090	64,910	
	20			±0.8	6,500	10,020	15,430	22,300	29,940	40,350	50,720	
	21~24	±0.2	9,480	15,670	25,940	36,490	51,210	68,730	86,840			
	25	±0.9	7,630	12,620	20,890	29,390	41,250	55,360	69,950			
	26~29	±0.2	10,800	16,660	27,170	38,790	51,810	69,450	87,510			
	30	±1.0	8,690	13,420	21,890	31,250	41,740	55,940	70,490			
ENPD (A2017P)	8~9	50~200	0~50	±0.2	7,220	—	—	—	—	—		
	10	50~600	0~100	±0.6	5,560	8,310	12,420	18,760	25,110	40,730	50,820	
	11~14			±0.2	8,290	13,470	21,910	32,610	44,550	72,360	91,150	
	15	100~800	0~100	±0.7	6,380	10,370	16,870	25,110	34,310	55,720	70,180	
	16~19			±0.2	11,520	17,650	27,030	41,160	55,620	74,820	94,970	
	20			±0.8	8,870	13,590	20,820	31,690	42,800	57,610	73,130	
	21~24	±0.2	13,910	21,330	32,710	48,660	67,350	90,420	115,250			
	25	±0.9	10,710	16,420	25,190	37,470	51,860	69,620	88,700			
	26~29	±0.2	15,640	24,410	38,120	57,050	79,070	106,280	135,510			
	30	±1.0	12,040	18,800	29,360	43,930	60,880	81,830	104,350			
ENPG (SUS303)	8~9	50~200	0~50	±0.2	8,840	—	—	—	—	—		
	10	50~600	0~100		8,840	19,980	—	—	—	—	—	
	11~15				11,720	26,120	—	—	—	—	—	
	16~20	14,630	31,880		—	—	—	—	—			
	21~25	16,900	37,640		—	—	—	—	—			
26~30	19,600	44,190	—	—	—	—	—					

■精級・フリーサイズ

Catalog No.		指定1mm単位			B 平行度	¥単価 1~4枚						
Type	T	D	d	D50 200		D201 300	D301 400	D401 500	D501 600	D601 700	D701 800	
ENPS (SS400)	8~9	50~200	0~50	0.012	5,230	—	—	—	—	—		
	10	50~600	0~100		6,340	10,200	16,480	23,980	32,390	—	—	
	11~15				6,980	11,230	18,070	27,390	36,220	—	—	
	16~20	100~800	0~100		7,430	11,790	18,710	28,580	39,750	54,200	69,770	
	21~25				7,990	12,830	20,580	31,270	41,730	56,720	71,950	
26~30	8,780			13,920	22,040	33,680	44,800	63,470	81,510			
ENPA (A5082P)	8~9	50~200	0~50	0.03	8,220	—	—	—	—	—		
	10	50~600	0~100	0.03	6,620	11,440	19,720	29,220	39,780	44,740	55,690	
	11~14			0.05	8,990	15,840	27,880	40,190	54,710	75,050	94,060	
	15	100~800	0~100	0.05	7,500	13,220	23,270	33,550	45,670	62,650	75,770	
	16~19			0.07	10,660	17,840	29,850	43,250	59,610	80,370	109,370	
	20			0.09	8,590	14,370	24,050	34,840	48,020	64,740	88,100	
	21~24	0.09	13,370	22,830	39,010	57,620	78,770	106,210	138,890			
	25	0.11	10,770	18,390	31,420	46,420	63,450	85,560	111,880			
	26~29	0.11	15,060	25,120	42,910	63,400	86,650	116,840	152,780			
	30	0.11	12,130	20,240	34,570	51,070	69,800	94,120	123,070			
ENPJ (A2017P)	8~9	50~200	0~50	0.03	10,230	—	—	—	—	—		
	10	50~600	0~100	0.03	7,870	13,550	23,300	34,260	47,470	—	—	
	11~14			0.05	12,460	21,710	37,840	55,610	77,460	—	—	
	15	100~800	0~100	0.05	9,590	16,710	29,130	42,820	59,650	—	—	
	16~19			0.07	15,720	25,730	42,120	63,190	87,330	117,760	158,150	
	20			0.09	12,100	19,810	32,430	48,660	67,240	90,670	121,770	
	21~24	0.09	17,460	28,800	47,540	70,840	99,060	133,630	174,440			
	25	0.11	13,440	22,180	36,600	54,540	76,270	102,900	134,320			
	26~29	0.11	19,440	32,160	53,210	78,520	109,780	147,870	194,700			
	30	0.11	14,970	24,760	40,970	60,460	84,530	113,860	149,920			
ENPU (SUS303)	8~9	50~200	0~50	0.03	10,620	—	—	—	—	—		
	10	50~600	0~100		10,620	23,980	—	—	—	—	—	
	11~15				14,080	31,340	—	—	—	—	—	
	16~20	18,190	39,670		—	—	—	—	—			
	21~25	20,270	45,180		—	—	—	—	—			
26~30	23,530	53,030	—	—	—	—	—					

<訂正用> 共通

