

M20のS寸数値訂正

型式		M×Pitch		D	d	F	B	C	S	m	並目¥単価 1~19コ			細目¥単価 1~19コ				
Type	M	並目	細目								BNG	BNGC	BNGS	BNR	BNRC	BNRS		
(並目) BNG BNGC BNGS (細目) BNR BNRC BNRS	3	M3×0.5	M3×0.35	11.5	4	10	5.5	3	0.5	M3 (セットピース付き)	400	500	600	390	500	600		
	4	M4×0.7	M4×0.5		5						390	490	590	380	490	590		
	5	M5×0.8	M5×0.5		13.5	9					11	360	450	540	350	450	540	
	6	M6×1.0	M6×0.75	14.5	10	12	360	450	540	350	450	540						
	8	M8×1.25	M8×1.0	17	13	14	340	430	510	330	430	510						
	10	M10×1.5	M10×1.0	20	16	17	340	430	510	330	430	510						
	12	M12×1.75	M12×1.0	22	17	19	8	5	1	M4 (セットピース付き)	370	470	560	360	470	560		
	15	—	M15×1.0	25	21	22	10	6			—	—	—	400	520	620	—	—
	16	M16×2.0	—								410	520	620	—	—	—		
	17	—	M17×1.0								—	—	—	420	530	630		
	20	M20×2.5	M20×1.0	35	26	30	13	8			430	540	650	420	540	650		
	24	M24×3.0	—	43	33	35	15	10			2	M5 (セットピース付き)	550	740	830	—	—	—
	25	—	M25×1.5										—	—	—	550	750	840
	30	M30×3.5	M30×1.5										640	850	960	640	850	960
	35	—	M35×1.5	48	39	40	20	14			M6 (セットピース付き)	—	—	—	730	980	1,100	
	40		M40×1.5		43	45						—	—	—	1,080	1,280	1,440	
	50		M50×1.5	66	61	63	25	16	—	—		—	1,450	1,840	2,060			

<訂正用>

