

P.534 <規格表>

基本定格荷重の表記を修正

■2列組合せ

Catalog No.		d	D	B	r (min)	r1 (min)	基本定格荷重		作用点a		取付関係寸法			質量 (g) (参考)	¥単価 1~9コ
ベアリング品番	2列組合せ						Cr(動) kN	Cor(静) kN	DB	DF	Ds (min.)	dh (max.)	R (max.)		
B7000	DB (背面) DF (正面)	10	26	8	0.3	0.15	8.75	5.2	18.4	2.4	11.2	24.8	0.15	46	1,780
B7200			30	9	0.6	0.3	8.8	5.4	20.5	2.5	12.5	27.5	0.3	58	2,200
B7001		12	28	8	0.3	0.15	9.4	5.95	19.5	3.5	13.2	26.8	0.15	50	1,820
B7201				10	0.6	0.3	13	8.05	22.7	2.7	14.5	29.5	0.3	70	2,260
B7002		15	32	9	0.3	0.15	9.95	6.85	22.6	4.6	16.2	30.8	0.15	70	2,100
B7202				11	0.6	0.3	14	9.3	25.4	3.4	17.5	32.5	0.3	92	2,590
B7003		17	35	10	0.3	0.15	10.4	7.65	25	5	18.2	33.8	0.15	92	2,150
B7203				40	0.6	0.3	17.6	12	28.5	4.5	19.5	37.5	0.3	128	2,680
B7004		20	42	12	0.6	0.3	17.6	13.2	29.9	5.9	22.5	39.5	0.3	160	2,480
B7204				14	1	0.6	23.5	16.6	33.3	5.3	25	42	0.6	200	3,060
B7005		25	47	12	0.6	0.3	18.3	14.8	32.8	8.8	27.5	44.5	0.3	186	2,760
B7205				52	15	1.0	0.6	26.3	20.5	37.2	7.2	30	47	0.6	250
B7006		30	55	13	1.0	0.6	23.6	20.2	37.5	11.5	35	50	0.6	270	3,030
B7206				62	16	1.0	0.6	36.5	29.5	42.6	10.6	35	57	0.6	386

kgf=N×0.101972