

ストップブロック 規格表および注文例を下記に修正

Catalog No.	A 選択	H 指定5mm単位	T		X	d ₁	d ₂	ℓ	¥単価 1~4コ				
			ザグリ穴	キリ穴					SBHB SBKHB	SBHM SBKHM	SBHNB SBKNHB	SBHNM SBKNHM	SBHU
(ザグリ穴) (キリ穴) SBHB SBKHB SBHM SBKHM SBHNB SBKNHB SBHNM SBKNHM SBHU	20 30 40 50	(5) 10~40	10	10	5	8	4.5	4.5	730	870	1,070	1,260	770
	30 40 50 60	(10) 15~50	15	A10	7	9.5	5.5	5.5	1,100	1,340	1,600	1,940	1,120
	30 40 50 60 70 80	(15) 20~50	20	15	8	11	6.5	6.5	1,410	1,690	2,050	2,450	1,370
	40 50 60 70 80 90 100	(20) 30~50	30	A15	10	14	9	9	1,480	1,770	2,150	2,570	1,440

ⓐA≥H ⓑHの()寸法はキリ穴タイプのみ適用

Catalog No.	A 選択	H 指定5mm単位	T		X	d ₁	d ₂	ℓ	N	¥単価 1~4コ			
			ザグリ穴 タップ付	キリ穴 タップ付						SBNB SBKNB	SBNM SBKNM	SBNNB SBKNNB	SBNNM SBKNHM
(ザグリ穴タップ付) (タップ付) SBNB SBKNB SBNM SBKNM SBNNB SBKNNB SBNNM SBKNHM	20 30 40 50	(5) 10~40	10	10	5	8	4.5	4.5	M 5	930	1,070	1,270	1,460
	30 40 50 60	(10) 15~50	15	A10	7	9.5	5.5	5.5	M 6	1,300	1,540	1,800	2,140
	30 40 50 60 70 80	(15) 20~50	20	15	8	11	6.5	6.5	M 8	1,610	1,890	2,250	2,650
	40 50 60 70 80 90 100	(20) 30~50	30	A15	10	14	9	9	M10	1,680	1,970	2,350	2,770

ⓐA≥H ⓑHの()寸法はタップ付タイプのみ適用



Order
注文例

Catalog No. — A — H — T
SBKHB — 40 — 5 — A10